

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504090

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 877.2 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504090

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504090

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46			
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34			
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4521
5°	4551
10°	4523
15°	4379
20°	4207
25°	3996
30°	3755
35°	3502
40°	3227
45°	2916
50°	2550
55°	2143
60°	1718
65°	1377
70°	1354
75°	1276
80°	1218
85°	1063

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2916 cd/sqm

TEST NUMBER: P1504090

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	4.9
10°-20°	118.2	13.5
20°-30°	165.3	18.8
30°-40°	177.9	20.3
40°-50°	157.6	18.0
50°-60°	109.9	12.5
60°-70°	60.4	6.9
70°-80°	34.8	4.0
80°-90°	10.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.3	37.2
0°-40°	504.2	57.5
0°-60°	771.7	88.0
0°-90°	877.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	877.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	449	
5°	450	43
15°	420	118
25°	360	165
35°	285	178
45°	205	158
55°	122	110
65°	58	60
75°	33	35
85°	9	10
90°	0	

TEST NUMBER: P1504090

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-900LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	449.0
2.5°	449.0
5°	450.3
7.5°	449.0
10°	442.4
12.5°	433.3
15°	420.1
17.5°	407.0
20°	392.6
22.5°	376.8
25°	359.7
27.5°	342.7
30°	323.0
32.5°	304.6
35°	284.9
37.5°	265.2
40°	245.5
42.5°	225.8
45°	204.8
47.5°	183.8
50°	162.8
52.5°	143.1
55°	122.1
57.5°	103.7
60°	85.3
62.5°	69.6
65°	57.8
67.5°	51.2
70°	46.0
72.5°	39.4
75°	32.8
77.5°	26.3
80°	21.0
82.5°	14.4
85°	9.2
87.5°	3.9
90°	0.0

(END OF REPORT)