

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504104

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (2700K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-20)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (2700K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, BRONZE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 562.1 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.22
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504104

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (2700K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504104

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (2700K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85		
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73		
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	65	62		
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48		
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	54	49	44	43		
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38		
8	64	51	43	37	62	50	42	37	49	42	37	47	41	36	46	41	36	34		
9	60	47	39	34	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	36	31	55	43	36	31	42	35	30	41	35	30	40	34	30	29		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2541
5°	2540
10°	2547
15°	2539
20°	2493
25°	2402
30°	2258
35°	2118
40°	1961
45°	1781
50°	1599
55°	1387
60°	1216
65°	1229
70°	1260
75°	1280
80°	1212
85°	1017

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1781 cd/sqm

TEST NUMBER: P1504104

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (2700K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.0	4.3
10°-20°	68.6	12.2
20°-30°	99.1	17.6
30°-40°	107.4	19.1
40°-50°	96.5	17.2
50°-60°	71.3	12.7
60°-70°	50.8	9.0
70°-80°	33.9	6.0
80°-90°	10.6	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	191.6	34.1
0°-40°	299.0	53.2
0°-60°	466.8	83.0
0°-90°	562.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	562.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	252	
5°	251	24
15°	244	69
25°	216	99
35°	172	107
45°	125	96
55°	79	71
65°	52	51
75°	33	34
85°	9	11
90°	0	

TEST NUMBER: P1504104

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (2700K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	252.4
2.5°	252.4
5°	251.3
7.5°	251.3
10°	249.1
12.5°	246.9
15°	243.6
17.5°	239.2
20°	232.7
22.5°	225.0
25°	216.2
27.5°	206.3
30°	194.2
32.5°	183.3
35°	172.3
37.5°	160.2
40°	149.2
42.5°	137.2
45°	125.1
47.5°	113.0
50°	102.1
52.5°	90.0
55°	79.0
57.5°	69.1
60°	60.4
62.5°	54.9
65°	51.6
67.5°	47.2
70°	42.8
72.5°	37.3
75°	32.9
77.5°	26.3
80°	20.9
82.5°	15.4
85°	8.8
87.5°	4.4
90°	0.0

(END OF REPORT)