

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503602

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (4000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (4000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, BRASS REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 120.5 lumens
Efficiency: N/A
Efficacy: 11.2 lumens/watt
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503602

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (4000K-1000LM)

Luminous Intensity Polar Plot



TEST NUMBER: P1503602

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (4000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	86	79	73	92	84	78	72	81	76	71	79	74	70	76	72	69	67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	64	61	59			
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52			
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46			
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			
9	61	48	40	35	59	48	40	35	47	40	35	45	39	35	44	39	35	33			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	31	30			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1277
5°	1269
10°	1265
15°	1366
20°	1516
25°	1715
30°	1926
35°	2048
40°	1904
45°	1544
50°	1060
55°	581
60°	407
65°	379
70°	352
75°	381
80°	408
85°	460

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1544 cd/sqm

TEST NUMBER: P1503602

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (4000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3.9	3.2
10°-20°	12.3	10.2
20°-30°	23.4	19.4
30°-40°	33.3	27.6
40°-50°	27.0	22.4
50°-60°	10.9	9.0
60°-70°	5.1	4.3
70°-80°	3.4	2.8
80°-90°	1.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	39.5	32.8
0°-40°	72.8	60.4
0°-60°	110.6	91.8
0°-90°	120.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	120.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	41	
5°	41	4
15°	43	12
25°	50	23
35°	54	33
45°	35	27
55°	11	11
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1503602

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (4000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	41.4
2.5°	41.2
5°	41.0
7.5°	40.7
10°	40.4
12.5°	41.4
15°	42.8
17.5°	44.4
20°	46.2
22.5°	48.1
25°	50.4
27.5°	52.3
30°	54.1
32.5°	55.6
35°	54.4
37.5°	51.7
40°	47.3
42.5°	41.8
45°	35.4
47.5°	28.8
50°	22.1
52.5°	15.8
55°	10.8
57.5°	8.1
60°	6.6
62.5°	5.8
65°	5.2
67.5°	4.5
70°	3.9
72.5°	3.6
75°	3.2
77.5°	2.9
80°	2.3
82.5°	2.1
85°	1.3
87.5°	0.3
90°	0.0

(END OF REPORT)