

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504149

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (2700K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-21)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (2700K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, BRASS REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 578.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.22
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504149

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (2700K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504149

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (2700K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85							
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73							
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	65	62							
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54							
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48							
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	54	49	44	42							
7	68	55	47	41	66	54	46	41	53	46	40	51	45	40	50	44	40	38							
8	64	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34							
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31							
10	56	43	36	31	55	43	35	31	42	35	30	41	35	30	40	34	30	28							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2608
5°	2607
10°	2614
15°	2597
20°	2563
25°	2463
30°	2322
35°	2172
40°	2019
45°	1844
50°	1634
55°	1445
60°	1261
65°	1256
70°	1292
75°	1280
80°	1212
85°	1144

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1844 cd/sqm

TEST NUMBER: P1504149

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (2700K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.5	4.2
10°-20°	70.2	12.1
20°-30°	101.7	17.6
30°-40°	110.6	19.1
40°-50°	99.7	17.2
50°-60°	73.7	12.8
60°-70°	52.3	9.1
70°-80°	34.6	6.0
80°-90°	10.6	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.4	34.0
0°-40°	307.0	53.1
0°-60°	480.4	83.1
0°-90°	578.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	578.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	259	
5°	258	25
15°	249	70
25°	222	102
35°	177	111
45°	130	100
55°	82	74
65°	53	52
75°	33	35
85°	10	11
90°	0	

TEST NUMBER: P1504149

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OT (2700K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	259.0
2.5°	259.0
5°	257.9
7.5°	256.8
10°	255.7
12.5°	252.4
15°	249.1
17.5°	244.7
20°	239.2
22.5°	230.5
25°	221.7
27.5°	211.8
30°	199.7
32.5°	188.8
35°	176.7
37.5°	165.7
40°	153.6
42.5°	141.6
45°	129.5
47.5°	117.4
50°	104.3
52.5°	93.3
55°	82.3
57.5°	71.3
60°	62.6
62.5°	57.1
65°	52.7
67.5°	48.3
70°	43.9
72.5°	38.4
75°	32.9
77.5°	27.4
80°	20.9
82.5°	15.4
85°	9.9
87.5°	3.3
90°	0.0

(END OF REPORT)