

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503617

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (4000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (4000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, WHITE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 290.8 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.45
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503617

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (4000K-1000LM)

Luminous Intensity Polar Plot



TEST NUMBER: P1503617

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (4000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62			
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	53			
5	78	66	57	51	76	64	56	50	62	55	50	60	54	49	59	53	49	47			
6	72	59	51	44	70	58	50	44	57	49	44	55	48	44	53	48	43	41			
7	67	54	45	39	65	53	45	39	52	44	39	50	44	39	49	43	38	37			
8	62	49	41	35	61	49	41	35	47	40	35	46	39	35	45	39	35	33			
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29			
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28	27			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2988
5°	2999
10°	3034
15°	3192
20°	3393
25°	3627
30°	3831
35°	3885
40°	3667
45°	3227
50°	2682
55°	2091
60°	1832
65°	1758
70°	1749
75°	1847
80°	2149
85°	2229

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3227 cd/sqm

TEST NUMBER: P1503617

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (4000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.2	3.2
10°-20°	28.5	9.8
20°-30°	49.2	16.9
30°-40°	63.8	21.9
40°-50°	56.9	19.6
50°-60°	36.2	12.4
60°-70°	24.0	8.3
70°-80°	16.5	5.7
80°-90°	6.6	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	86.9	29.9
0°-40°	150.7	51.8
0°-60°	243.7	83.8
0°-90°	290.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	290.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	97	
5°	97	9
15°	100	28
25°	107	49
35°	103	64
45°	74	57
55°	39	36
65°	24	24
75°	16	17
85°	6	7
90°	0	

TEST NUMBER: P1503617

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (4000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	96.9
2.5°	96.8
5°	96.9
7.5°	96.9
10°	96.9
12.5°	98.4
15°	100.0
17.5°	101.6
20°	103.4
22.5°	105.2
25°	106.6
27.5°	107.4
30°	107.6
32.5°	106.8
35°	103.2
37.5°	98.1
40°	91.1
42.5°	82.9
45°	74.0
47.5°	65.3
50°	55.9
52.5°	47.0
55°	38.9
57.5°	33.6
60°	29.7
62.5°	26.7
65°	24.1
67.5°	21.6
70°	19.4
72.5°	17.4
75°	15.5
77.5°	13.9
80°	12.1
82.5°	10.0
85°	6.3
87.5°	1.8
90°	0.0

(END OF REPORT)