

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504164

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504164
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-16)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 883.2 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.38
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504164

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504164

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	94	88	83	99	93	87	82	89	84	80	86	82	79	83	80	77	75		
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	61	55	51	49		
6	73	61	52	46	72	60	52	46	58	51	46	57	50	45	55	49	45	43		
7	68	55	47	41	66	55	47	41	53	46	41	52	45	40	50	45	40	38		
8	63	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34		
9	59	46	39	33	58	46	38	33	45	38	33	44	37	33	43	37	33	31		
10	56	43	35	30	54	42	35	30	41	35	30	40	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3646
5°	3639
10°	3636
15°	3627
20°	3610
25°	3596
30°	3560
35°	3534
40°	3520
45°	3437
50°	3197
55°	2812
60°	2253
65°	1594
70°	871
75°	727
80°	765
85°	762

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3437 cd/sqm

TEST NUMBER: P1504164

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.2	3.9
10°-20°	98.2	11.1
20°-30°	148.9	16.9
30°-40°	180.1	20.4
40°-50°	184.8	20.9
50°-60°	142.2	16.1
60°-70°	67.1	7.6
70°-80°	20.7	2.3
80°-90°	6.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.4	31.9
0°-40°	461.4	52.2
0°-60°	788.4	89.3
0°-90°	883.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	883.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	362	
5°	360	34
15°	348	98
25°	324	149
35°	288	180
45°	241	185
55°	160	142
65°	67	67
75°	19	21
85°	7	7
90°	0	

TEST NUMBER: P1504164

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-750LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	362.1
2.5°	361.0
5°	360.0
7.5°	357.8
10°	355.6
12.5°	352.3
15°	347.9
17.5°	343.5
20°	336.9
22.5°	330.3
25°	323.7
27.5°	315.0
30°	306.2
32.5°	297.4
35°	287.5
37.5°	277.6
40°	267.8
42.5°	256.8
45°	241.4
47.5°	223.9
50°	204.1
52.5°	183.3
55°	160.2
57.5°	136.1
60°	111.9
62.5°	88.9
65°	66.9
67.5°	46.1
70°	29.6
72.5°	21.9
75°	18.7
77.5°	16.5
80°	13.2
82.5°	9.9
85°	6.6
87.5°	2.2
90°	0.0

(END OF REPORT)