

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503605

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (5000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (5000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, BRASS REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 124.0 lumens
Efficiency: N/A
Efficacy: 11.5 lumens/watt
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503605

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (5000K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503605

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (5000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	86	79	73	92	84	78	72	81	76	71	79	74	70	76	72	69	67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59			
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52			
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46			
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			
9	61	48	40	35	59	48	40	35	47	40	35	45	39	35	44	39	35	33			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	31	30			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1314
5°	1306
10°	1303
15°	1408
20°	1562
25°	1766
30°	1983
35°	2108
40°	1960
45°	1587
50°	1094
55°	597
60°	419
65°	387
70°	361
75°	393
80°	408
85°	460

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1587 cd/sqm

TEST NUMBER: P1503605

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (5000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.0	3.2
10°-20°	12.6	10.2
20°-30°	24.1	19.4
30°-40°	34.2	27.6
40°-50°	27.8	22.4
50°-60°	11.2	9.0
60°-70°	5.3	4.3
70°-80°	3.5	2.8
80°-90°	1.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	40.7	32.8
0°-40°	74.9	60.4
0°-60°	113.9	91.8
0°-90°	124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	124.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	43	
5°	42	4
15°	44	13
25°	52	24
35°	56	34
45°	36	28
55°	11	11
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1503605

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (5000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	42.6
2.5°	42.4
5°	42.2
7.5°	41.9
10°	41.6
12.5°	42.6
15°	44.1
17.5°	45.7
20°	47.6
22.5°	49.5
25°	51.9
27.5°	53.9
30°	55.7
32.5°	57.2
35°	56.0
37.5°	53.2
40°	48.7
42.5°	43.1
45°	36.4
47.5°	29.6
50°	22.8
52.5°	16.3
55°	11.1
57.5°	8.3
60°	6.8
62.5°	6.0
65°	5.3
67.5°	4.7
70°	4.0
72.5°	3.7
75°	3.3
77.5°	3.0
80°	2.3
82.5°	2.2
85°	1.3
87.5°	0.3
90°	0.0

(END OF REPORT)