

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504194

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (2700K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-19)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHITE-XX-OT (2700K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 646.5 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.24
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504194

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (2700K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504194

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHITE-XX-OT (2700K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62			
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54			
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47			
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34			
9	59	46	38	33	58	45	38	33	44	37	33	43	37	32	42	36	32	30			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2806
5°	2817
10°	2817
15°	2803
20°	2763
25°	2670
30°	2539
35°	2401
40°	2250
45°	2063
50°	1856
55°	1657
60°	1480
65°	1491
70°	1519
75°	1494
80°	1461
85°	1271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2063 cd/sqm

TEST NUMBER: P1504194

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (2700K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	4.1
10°-20°	75.8	11.7
20°-30°	110.5	17.1
30°-40°	122.0	18.9
40°-50°	111.6	17.3
50°-60°	84.9	13.1
60°-70°	62.0	9.6
70°-80°	40.5	6.3
80°-90°	12.7	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.7	32.9
0°-40°	334.8	51.8
0°-60°	531.3	82.2
0°-90°	646.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	646.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	279	
5°	279	26
15°	269	76
25°	240	110
35°	195	122
45°	145	112
55°	94	85
65°	63	62
75°	38	41
85°	11	13
90°	0	

TEST NUMBER: P1504194

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (2700K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	278.7
2.5°	278.7
5°	278.7
7.5°	276.6
10°	275.5
12.5°	273.3
15°	268.9
17.5°	264.5
20°	257.9
22.5°	250.2
25°	240.3
27.5°	230.5
30°	218.4
32.5°	207.4
35°	195.3
37.5°	183.3
40°	171.2
42.5°	158.0
45°	144.9
47.5°	131.7
50°	118.5
52.5°	106.5
55°	94.4
57.5°	83.4
60°	73.5
62.5°	68.0
65°	62.6
67.5°	57.1
70°	51.6
72.5°	45.0
75°	38.4
77.5°	31.8
80°	25.2
82.5°	18.7
85°	11.0
87.5°	4.4
90°	0.0

(END OF REPORT)