

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503622

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (5000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (5000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 230.7 lumens
Efficiency: N/A
Efficacy: 28.1 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.45
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503622

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (5000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503622

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (5000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62			
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	53			
5	78	66	57	51	76	64	56	50	62	55	50	60	54	49	59	53	49	47			
6	72	59	51	44	70	58	50	44	57	49	44	55	48	44	53	48	43	41			
7	67	54	45	39	65	53	45	39	52	44	39	50	44	39	49	43	38	37			
8	62	49	41	35	61	49	41	35	47	40	35	46	39	35	45	39	35	33			
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29			
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28	27			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2371
5°	2380
10°	2408
15°	2532
20°	2691
25°	2878
30°	3037
35°	3083
40°	2910
45°	2560
50°	2125
55°	1661
60°	1455
65°	1394
70°	1388
75°	1465
80°	1705
85°	1769

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2560 cd/sqm

TEST NUMBER: P1503622

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (5000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.3	3.2
10°-20°	22.6	9.8
20°-30°	39.0	16.9
30°-40°	50.6	21.9
40°-50°	45.1	19.6
50°-60°	28.7	12.5
60°-70°	19.0	8.3
70°-80°	13.1	5.7
80°-90°	5.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	68.9	29.9
0°-40°	119.5	51.8
0°-60°	193.4	83.8
0°-90°	230.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	230.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	77	
5°	77	7
15°	79	23
25°	85	39
35°	82	51
45°	59	45
55°	31	29
65°	19	19
75°	12	13
85°	5	5
90°	0	

TEST NUMBER: P1503622

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (5000K-800LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	76.9
2.5°	76.8
5°	76.9
7.5°	76.9
10°	76.9
12.5°	78.0
15°	79.3
17.5°	80.6
20°	82.0
22.5°	83.4
25°	84.6
27.5°	85.2
30°	85.3
32.5°	84.7
35°	81.9
37.5°	77.8
40°	72.3
42.5°	65.7
45°	58.7
47.5°	51.8
50°	44.3
52.5°	37.3
55°	30.9
57.5°	26.7
60°	23.6
62.5°	21.1
65°	19.1
67.5°	17.2
70°	15.4
72.5°	13.8
75°	12.3
77.5°	11.0
80°	9.6
82.5°	7.9
85°	5.0
87.5°	1.4
90°	0.0

(END OF REPORT)