

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503987

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (3000K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (3000K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, BRASS REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 699.9 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503987

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (3000K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503987

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (3000K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89		
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77		
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67		
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	54	64	58	54	63	57	53	51		
6	75	63	55	49	73	62	54	49	60	53	48	58	52	48	57	52	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40		
8	65	52	44	39	63	52	44	39	50	43	39	49	43	38	48	42	38	36		
9	61	48	40	35	59	47	40	35	46	40	35	45	39	35	44	39	35	33		
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	31	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3111
5°	3103
10°	3098
15°	3086
20°	3065
25°	3033
30°	3000
35°	2962
40°	2918
45°	2834
50°	2569
55°	2177
60°	1631
65°	953
70°	294
75°	156
80°	174
85°	231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2834 cd/sqm

TEST NUMBER: P1503987

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (3000K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.2	4.2
10°-20°	83.5	11.9
20°-30°	125.9	18.0
30°-40°	150.7	21.5
40°-50°	151.9	21.7
50°-60°	110.2	15.7
60°-70°	41.4	5.9
70°-80°	5.1	0.7
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	238.6	34.1
0°-40°	389.2	55.6
0°-60°	651.4	93.1
0°-90°	699.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	699.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	309	
5°	307	29
15°	296	84
25°	273	126
35°	241	151
45°	199	152
55°	124	110
65°	40	41
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1503987

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-ND (3000K-750LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	309
2.5°	308
5°	307
7.5°	305
10°	303
12.5°	301
15°	296
17.5°	291
20°	286
22.5°	280
25°	273
27.5°	266
30°	258
32.5°	249
35°	241
37.5°	232
40°	222
42.5°	213
45°	199
47.5°	183
50°	164
52.5°	145
55°	124
57.5°	103
60°	81
62.5°	60
65°	40
67.5°	23
70°	10
72.5°	5
75°	4
77.5°	4
80°	3
82.5°	3
85°	2
87.5°	1
90°	0

(END OF REPORT)