

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504033

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-16)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 962.8 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.38
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504033

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504033

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	94	88	83	99	93	87	82	89	84	80	86	82	79	83	80	77	75		
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	61	55	51	49		
6	73	61	52	46	72	60	52	46	58	51	46	57	50	45	55	49	45	43		
7	68	55	47	41	66	55	47	41	53	46	41	52	45	40	50	45	40	38		
8	63	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34		
9	59	46	39	33	58	46	38	33	45	38	33	44	37	33	43	37	33	31		
10	56	43	35	30	54	42	35	30	41	35	30	40	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3975
5°	3966
10°	3963
15°	3954
20°	3936
25°	3921
30°	3881
35°	3854
40°	3837
45°	3748
50°	3485
55°	3067
60°	2457
65°	1739
70°	951
75°	790
80°	835
85°	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3748 cd/sqm

TEST NUMBER: P1504033

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.3	3.9
10°-20°	107.1	11.1
20°-30°	162.4	16.9
30°-40°	196.3	20.4
40°-50°	201.5	20.9
50°-60°	155.0	16.1
60°-70°	73.2	7.6
70°-80°	22.5	2.3
80°-90°	7.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.7	31.9
0°-40°	503.0	52.2
0°-60°	859.6	89.3
0°-90°	962.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	962.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	395	
5°	392	37
15°	379	107
25°	353	162
35°	314	196
45°	263	201
55°	175	155
65°	73	73
75°	20	23
85°	7	8
90°	0	

TEST NUMBER: P1504033

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-900LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	394.8
2.5°	393.6
5°	392.4
7.5°	390.0
10°	387.6
12.5°	384.0
15°	379.3
17.5°	374.5
20°	367.3
22.5°	360.1
25°	352.9
27.5°	343.4
30°	333.8
32.5°	324.2
35°	313.5
37.5°	302.7
40°	291.9
42.5°	280.0
45°	263.2
47.5°	244.1
50°	222.5
52.5°	199.8
55°	174.7
57.5°	148.4
60°	122.0
62.5°	96.9
65°	73.0
67.5°	50.2
70°	32.3
72.5°	23.9
75°	20.3
77.5°	17.9
80°	14.4
82.5°	10.8
85°	7.2
87.5°	2.4
90°	0.0

(END OF REPORT)