

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504136

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-24)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1277.7 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504136

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504136

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66		
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	45		
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6588
5°	6613
10°	6574
15°	6368
20°	6101
25°	5824
30°	5459
35°	5099
40°	4708
45°	4242
50°	3722
55°	3144
60°	2505
65°	2020
70°	1999
75°	1906
80°	1751
85°	1525

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4242 cd/sqm

TEST NUMBER: P1504136

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.2	4.9
10°-20°	171.6	13.4
20°-30°	240.1	18.8
30°-40°	258.8	20.3
40°-50°	229.4	18.0
50°-60°	160.6	12.6
60°-70°	88.5	6.9
70°-80°	51.7	4.0
80°-90°	14.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	473.8	37.1
0°-40°	732.6	57.3
0°-60°	1122.6	87.9
0°-90°	1277.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1277.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	654	
5°	654	62
15°	611	172
25°	524	240
35°	415	259
45°	298	229
55°	179	161
65°	85	89
75°	49	52
85°	13	15
90°	0	

TEST NUMBER: P1504136

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1200LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	654.3
2.5°	654.3
5°	654.3
7.5°	652.4
10°	643.0
12.5°	629.8
15°	610.9
17.5°	590.2
20°	569.4
22.5°	546.8
25°	524.2
27.5°	495.9
30°	469.5
32.5°	441.2
35°	414.8
37.5°	386.5
40°	358.2
42.5°	328.1
45°	297.9
47.5°	267.7
50°	237.6
52.5°	209.3
55°	179.1
57.5°	150.8
60°	124.4
62.5°	101.8
65°	84.8
67.5°	75.4
70°	67.9
72.5°	58.5
75°	49.0
77.5°	39.6
80°	30.2
82.5°	20.7
85°	13.2
87.5°	5.7
90°	0.0

(END OF REPORT)