

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503758

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 923.9 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.3
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503758

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503758

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	83	77	72	81	75	70	78	73	69	76	71	68	66		
4	87	76	69	63	85	75	68	62	73	66	61	70	65	61	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	54	49	73	62	54	48	60	53	48	58	52	48	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	41		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12951
5°	12948
10°	12891
15°	12830
20°	12755
25°	12609
30°	12434
35°	12152
40°	11468
45°	10488
50°	9163
55°	7613
60°	5686
65°	3729
70°	2966
75°	2943
80°	2930
85°	2335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10488 cd/sqm

TEST NUMBER: P1503758

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.7	4.3
10°-20°	113.4	12.3
20°-30°	170.6	18.5
30°-40°	200.6	21.7
40°-50°	184.4	20.0
50°-60°	126.2	13.7
60°-70°	54.8	5.9
70°-80°	26.1	2.8
80°-90°	8.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	323.8	35.0
0°-40°	524.3	56.8
0°-60°	835.0	90.4
0°-90°	923.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	923.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	420	
5°	418	40
15°	402	113
25°	371	171
35°	323	201
45°	240	184
55°	142	126
65°	51	55
75°	25	26
85°	7	8
90°	0	

TEST NUMBER: P1503758

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (2700K-1000LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	420.0
2.5°	418.3
5°	418.3
7.5°	415.0
10°	411.7
12.5°	408.4
15°	401.9
17.5°	395.3
20°	388.7
22.5°	378.8
25°	370.6
27.5°	360.7
30°	349.2
32.5°	337.6
35°	322.8
37.5°	304.7
40°	284.9
42.5°	263.5
45°	240.5
47.5°	215.8
50°	191.0
52.5°	166.3
55°	141.6
57.5°	116.9
60°	92.2
62.5°	70.8
65°	51.1
67.5°	37.9
70°	32.9
72.5°	28.0
75°	24.7
77.5°	21.4
80°	16.5
82.5°	11.5
85°	6.6
87.5°	3.3
90°	0.0

(END OF REPORT)