

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504181

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-22)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1357.5 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.19
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504181

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504181

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87		
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75		
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50		
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40		
8	65	52	45	39	64	52	44	39	50	44	39	49	43	39	48	43	38	37		
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33		
10	57	45	38	33	56	44	37	32	43	37	32	43	37	32	42	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6854
5°	6880
10°	6843
15°	6643
20°	6343
25°	6075
30°	5744
35°	5353
40°	4982
45°	4511
50°	3987
55°	3376
60°	2735
65°	2292
70°	2220
75°	2128
80°	1966
85°	1744

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4511 cd/sqm

TEST NUMBER: P1504181

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	4.8
10°-20°	178.9	13.2
20°-30°	251.1	18.5
30°-40°	272.4	20.1
40°-50°	244.0	18.0
50°-60°	173.0	12.7
60°-70°	98.8	7.3
70°-80°	57.2	4.2
80°-90°	17.4	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.7	36.4
0°-40°	767.0	56.5
0°-60°	1184.0	87.2
0°-90°	1357.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1357.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	681	
5°	681	65
15°	637	179
25°	547	251
35°	436	272
45°	317	244
55°	192	173
65°	96	99
75°	55	57
85°	15	17
90°	0	

TEST NUMBER: P1504181

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-1200LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	680.7
2.5°	680.7
5°	680.7
7.5°	678.8
10°	669.3
12.5°	656.2
15°	637.3
17.5°	616.6
20°	592.0
22.5°	571.3
25°	546.8
27.5°	520.4
30°	494.0
32.5°	463.8
35°	435.5
37.5°	407.3
40°	379.0
42.5°	346.9
45°	316.8
47.5°	286.6
50°	254.5
52.5°	224.4
55°	192.3
57.5°	164.0
60°	135.8
62.5°	113.1
65°	96.2
67.5°	84.8
70°	75.4
72.5°	64.1
75°	54.7
77.5°	43.4
80°	33.9
82.5°	24.5
85°	15.1
87.5°	7.5
90°	0.0

(END OF REPORT)