

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503818

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-14)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 782.0 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503818

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503818

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
R	C																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13309
5°	13304
10°	13232
15°	12741
20°	12089
25°	11429
30°	10611
35°	9720
40°	8795
45°	7719
50°	6496
55°	5242
60°	4120
65°	3692
70°	3579
75°	3443
80°	3214
85°	2547

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7719 cd/sqm

TEST NUMBER: P1503818

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.9	5.2
10°-20°	112.0	14.3
20°-30°	154.0	19.7
30°-40°	161.3	20.6
40°-50°	135.8	17.4
50°-60°	88.5	11.3
60°-70°	50.7	6.5
70°-80°	30.0	3.8
80°-90°	8.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.9	39.2
0°-40°	468.1	59.9
0°-60°	692.5	88.6
0°-90°	782.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	782.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	432	
5°	430	41
15°	399	112
25°	336	154
35°	258	161
45°	177	136
55°	98	89
65°	51	51
75°	29	30
85°	7	9
90°	0	

TEST NUMBER: P1503818

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-1000LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	431.6
2.5°	431.6
5°	429.8
7.5°	429.8
10°	422.6
12.5°	411.7
15°	399.1
17.5°	384.7
20°	368.4
22.5°	352.1
25°	335.9
27.5°	317.8
30°	298.0
32.5°	278.1
35°	258.2
37.5°	238.4
40°	218.5
42.5°	196.8
45°	177.0
47.5°	155.3
50°	135.4
52.5°	117.4
55°	97.5
57.5°	81.3
60°	66.8
62.5°	56.0
65°	50.6
67.5°	45.1
70°	39.7
72.5°	34.3
75°	28.9
77.5°	21.7
80°	18.1
82.5°	12.6
85°	7.2
87.5°	3.6
90°	0.0

(END OF REPORT)