

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504183

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-22)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 958.9 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.19
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504183

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504183

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87		
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75		
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50		
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40		
8	65	52	45	39	64	52	44	39	50	44	39	49	43	39	48	43	38	37		
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33		
10	57	45	38	33	56	44	37	32	43	37	32	43	37	32	42	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4841
5°	4860
10°	4834
15°	4693
20°	4481
25°	4291
30°	4058
35°	3782
40°	3519
45°	3187
50°	2816
55°	2386
60°	1931
65°	1618
70°	1569
75°	1502
80°	1392
85°	1236

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3187 cd/sqm

TEST NUMBER: P1504183

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	4.8
10°-20°	126.4	13.2
20°-30°	177.4	18.5
30°-40°	192.4	20.1
40°-50°	172.4	18.0
50°-60°	122.2	12.7
60°-70°	69.8	7.3
70°-80°	40.4	4.2
80°-90°	12.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.4	36.4
0°-40°	541.8	56.5
0°-60°	836.4	87.2
0°-90°	958.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	958.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	481	
5°	481	46
15°	450	126
25°	386	177
35°	308	192
45°	224	172
55°	136	122
65°	68	70
75°	39	40
85°	11	12
90°	0	

TEST NUMBER: P1504183

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-900LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	480.8
2.5°	480.8
5°	480.8
7.5°	479.5
10°	472.8
12.5°	463.5
15°	450.2
17.5°	435.5
20°	418.2
22.5°	403.6
25°	386.2
27.5°	367.6
30°	349.0
32.5°	327.6
35°	307.7
37.5°	287.7
40°	267.7
42.5°	245.1
45°	223.8
47.5°	202.4
50°	179.8
52.5°	158.5
55°	135.9
57.5°	115.9
60°	95.9
62.5°	79.9
65°	67.9
67.5°	59.9
70°	53.3
72.5°	45.3
75°	38.6
77.5°	30.6
80°	24.0
82.5°	17.3
85°	10.7
87.5°	5.3
90°	0.0

(END OF REPORT)