

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503908

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 876.4 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503908

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503908

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66			
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14533
5°	14477
10°	14363
15°	13893
20°	13215
25°	12473
30°	11640
35°	10740
40°	9741
45°	8661
50°	7450
55°	6215
60°	5014
65°	4480
70°	4237
75°	3872
80°	3534
85°	3184

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8661 cd/sqm

TEST NUMBER: P1503908

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	5.1
10°-20°	122.0	13.9
20°-30°	168.5	19.2
30°-40°	178.1	20.3
40°-50°	152.9	17.4
50°-60°	104.1	11.9
60°-70°	61.4	7.0
70°-80°	35.0	4.0
80°-90°	10.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.9	38.2
0°-40°	512.9	58.5
0°-60°	769.9	87.8
0°-90°	876.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	876.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	471	
5°	468	44
15°	435	122
25°	367	168
35°	285	178
45°	199	153
55°	116	104
65°	61	61
75°	32	35
85°	9	10
90°	0	

TEST NUMBER: P1503908

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	471.3
2.5°	469.5
5°	467.7
7.5°	465.9
10°	458.7
12.5°	447.9
15°	435.2
17.5°	419.0
20°	402.7
22.5°	384.6
25°	366.6
27.5°	348.5
30°	326.9
32.5°	307.0
35°	285.3
37.5°	263.7
40°	242.0
42.5°	220.3
45°	198.6
47.5°	177.0
50°	155.3
52.5°	135.4
55°	115.6
57.5°	97.5
60°	81.3
62.5°	68.6
65°	61.4
67.5°	54.2
70°	47.0
72.5°	39.7
75°	32.5
77.5°	27.1
80°	19.9
82.5°	14.4
85°	9.0
87.5°	3.6
90°	0.0

(END OF REPORT)