

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504006

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (3500K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-24)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (3500K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 813.9 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504006

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (3500K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504006

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (3500K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66		
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	45		
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4197
5°	4213
10°	4188
15°	4057
20°	3886
25°	3710
30°	3478
35°	3248
40°	2999
45°	2703
50°	2370
55°	2003
60°	1597
65°	1287
70°	1272
75°	1214
80°	1113
85°	970

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2703 cd/sqm

TEST NUMBER: P1504006

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (3500K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	4.9
10°-20°	109.3	13.4
20°-30°	152.9	18.8
30°-40°	164.8	20.3
40°-50°	146.2	18.0
50°-60°	102.3	12.6
60°-70°	56.4	6.9
70°-80°	32.9	4.0
80°-90°	9.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	301.8	37.1
0°-40°	466.7	57.3
0°-60°	715.1	87.9
0°-90°	813.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	813.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	417	
5°	417	40
15°	389	109
25°	334	153
35°	264	165
45°	190	146
55°	114	102
65°	54	56
75°	31	33
85°	8	9
90°	0	

TEST NUMBER: P1504006

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OC (3500K-900LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	416.8
2.5°	416.8
5°	416.8
7.5°	415.6
10°	409.6
12.5°	401.2
15°	389.2
17.5°	375.9
20°	362.7
22.5°	348.3
25°	333.9
27.5°	315.9
30°	299.1
32.5°	281.1
35°	264.2
37.5°	246.2
40°	228.2
42.5°	209.0
45°	189.8
47.5°	170.6
50°	151.3
52.5°	133.3
55°	114.1
57.5°	96.1
60°	79.3
62.5°	64.9
65°	54.0
67.5°	48.0
70°	43.2
72.5°	37.2
75°	31.2
77.5°	25.2
80°	19.2
82.5°	13.2
85°	8.4
87.5°	3.6
90°	0.0

(END OF REPORT)