

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504021

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OT (3500K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-21)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OT (3500K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, BRASS REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 632.5 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.22
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504021

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OT (3500K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504021

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OT (3500K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85							
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73							
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	65	62							
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54							
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48							
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	54	49	44	42							
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38							
8	64	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34							
9	60	47	39	34	58	46	39	33	45	38	33	44	38	33	43	37	33	31							
10	56	43	36	31	55	43	35	31	42	35	30	41	35	30	40	34	30	28							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2855
5°	2853
10°	2862
15°	2842
20°	2805
25°	2695
30°	2542
35°	2377
40°	2211
45°	2018
50°	1787
55°	1582
60°	1379
65°	1375
70°	1413
75°	1401
80°	1322
85°	1248

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2018 cd/sqm

TEST NUMBER: P1504021

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OT (3500K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.9	4.2
10°-20°	76.8	12.1
20°-30°	111.3	17.6
30°-40°	121.1	19.1
40°-50°	109.1	17.2
50°-60°	80.7	12.8
60°-70°	57.3	9.1
70°-80°	37.8	6.0
80°-90°	11.6	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	215.0	34.0
0°-40°	336.1	53.1
0°-60°	525.8	83.1
0°-90°	632.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	632.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	284	
5°	282	27
15°	273	77
25°	243	111
35°	193	121
45°	142	109
55°	90	81
65°	58	57
75°	36	38
85°	11	12
90°	0	

TEST NUMBER: P1504021

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRSS-XX-OT (3500K-900LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	283.5
2.5°	283.5
5°	282.3
7.5°	281.1
10°	279.9
12.5°	276.3
15°	272.6
17.5°	267.8
20°	261.8
22.5°	252.2
25°	242.6
27.5°	231.8
30°	218.6
32.5°	206.6
35°	193.4
37.5°	181.4
40°	168.2
42.5°	154.9
45°	141.7
47.5°	128.5
50°	114.1
52.5°	102.1
55°	90.1
57.5°	78.1
60°	68.5
62.5°	62.5
65°	57.7
67.5°	52.8
70°	48.0
72.5°	42.0
75°	36.0
77.5°	30.0
80°	22.8
82.5°	16.8
85°	10.8
87.5°	3.6
90°	0.0

(END OF REPORT)