

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503733

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (3000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-15)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (3000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 539.4 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503733

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (3000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503733

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (3000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	68	66			
4	88	77	69	63	85	76	69	63	73	67	62	71	66	61	69	64	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9155
5°	9153
10°	9106
15°	8773
20°	8335
25°	7849
30°	7296
35°	6697
40°	6026
45°	5299
50°	4471
55°	3629
60°	2874
65°	2598
70°	2434
75°	2335
80°	2184
85°	1734

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5299 cd/sqm

TEST NUMBER: P1503733

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (3000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.1	5.2
10°-20°	77.1	14.3
20°-30°	106.0	19.6
30°-40°	111.0	20.6
40°-50°	93.7	17.4
50°-60°	61.2	11.4
60°-70°	35.5	6.6
70°-80°	20.7	3.8
80°-90°	6.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.2	39.2
0°-40°	322.2	59.7
0°-60°	477.1	88.5
0°-90°	539.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	539.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	297	
5°	296	28
15°	275	77
25°	231	106
35°	178	111
45°	122	94
55°	68	61
65°	36	36
75°	20	21
85°	5	6
90°	0	

TEST NUMBER: P1503733

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (3000K-800LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	296.9
2.5°	296.9
5°	295.7
7.5°	294.5
10°	290.8
12.5°	283.4
15°	274.8
17.5°	265.0
20°	254.0
22.5°	242.9
25°	230.7
27.5°	218.4
30°	204.9
32.5°	191.4
35°	177.9
37.5°	164.4
40°	149.7
42.5°	136.2
45°	121.5
47.5°	108.0
50°	93.2
52.5°	81.0
55°	67.5
57.5°	56.4
60°	46.6
62.5°	39.3
65°	35.6
67.5°	31.9
70°	27.0
72.5°	23.3
75°	19.6
77.5°	15.9
80°	12.3
82.5°	8.6
85°	4.9
87.5°	2.5
90°	0.0

(END OF REPORT)