

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503762

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 542.2 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.3
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503762

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503762

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	83	77	72	81	75	70	78	73	69	76	71	68	66		
4	87	76	69	63	85	75	68	62	73	66	61	70	65	61	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	54	49	73	62	54	48	60	53	48	58	52	48	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	41		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7601
5°	7599
10°	7568
15°	7531
20°	7485
25°	7400
30°	7296
35°	7134
40°	6730
45°	6153
50°	5378
55°	4468
60°	3336
65°	2189
70°	1740
75°	1728
80°	1723
85°	1380

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6153 cd/sqm

TEST NUMBER: P1503762

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.3	4.3
10°-20°	66.6	12.3
20°-30°	100.1	18.5
30°-40°	117.7	21.7
40°-50°	108.2	20.0
50°-60°	74.1	13.7
60°-70°	32.2	5.9
70°-80°	15.3	2.8
80°-90°	4.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.0	35.0
0°-40°	307.7	56.8
0°-60°	490.0	90.4
0°-90°	542.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	542.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	246	
5°	246	23
15°	236	67
25°	218	100
35°	190	118
45°	141	108
55°	83	74
65°	30	32
75°	14	15
85°	4	5
90°	0	

TEST NUMBER: P1503762

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3000K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	246.5
2.5°	245.5
5°	245.5
7.5°	243.6
10°	241.7
12.5°	239.7
15°	235.9
17.5°	232.0
20°	228.1
22.5°	222.3
25°	217.5
27.5°	211.7
30°	204.9
32.5°	198.2
35°	189.5
37.5°	178.8
40°	167.2
42.5°	154.7
45°	141.1
47.5°	126.6
50°	112.1
52.5°	97.6
55°	83.1
57.5°	68.6
60°	54.1
62.5°	41.6
65°	30.0
67.5°	22.2
70°	19.3
72.5°	16.4
75°	14.5
77.5°	12.6
80°	9.7
82.5°	6.8
85°	3.9
87.5°	1.9
90°	0.0

(END OF REPORT)