

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504095

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-750LM)

Issue Date: 7/28/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1504095  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/28/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-750LM)  
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR  
LIGHT LEVEL 1 - 750 NOMINAL LUMENS  
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 751.8 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18  
Luminous Opening: Circular (Dia: 1.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1504095

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-750LM)

### Luminous Intensity Polar Plot





TEST NUMBER: P1504095

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-750LM)

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |   |
| 1   | 110 | 106 | 103 | 99  | 108 | 104 | 101 | 98  | 100 | 97  | 95  | 96  | 94  | 92  | 92  | 91  | 89  | 87  |  |  |   |
| 2   | 102 | 95  | 89  | 84  | 99  | 93  | 87  | 83  | 89  | 85  | 81  | 86  | 82  | 79  | 83  | 80  | 77  | 75  |  |  |   |
| 3   | 94  | 85  | 77  | 72  | 92  | 83  | 76  | 71  | 80  | 75  | 70  | 78  | 73  | 69  | 75  | 71  | 68  | 66  |  |  |   |
| 4   | 87  | 76  | 68  | 62  | 85  | 75  | 68  | 62  | 73  | 66  | 61  | 70  | 65  | 60  | 68  | 63  | 60  | 58  |  |  |   |
| 5   | 81  | 69  | 61  | 55  | 79  | 68  | 60  | 55  | 66  | 59  | 54  | 64  | 58  | 54  | 62  | 57  | 53  | 51  |  |  |   |
| 6   | 75  | 63  | 55  | 49  | 73  | 62  | 54  | 49  | 60  | 53  | 48  | 59  | 53  | 48  | 57  | 52  | 47  | 46  |  |  |   |
| 7   | 70  | 58  | 49  | 44  | 68  | 57  | 49  | 44  | 55  | 48  | 43  | 54  | 48  | 43  | 53  | 47  | 43  | 41  |  |  |   |
| 8   | 65  | 53  | 45  | 40  | 64  | 52  | 45  | 40  | 51  | 44  | 39  | 50  | 44  | 39  | 49  | 43  | 39  | 37  |  |  |   |
| 9   | 61  | 49  | 41  | 36  | 60  | 48  | 41  | 36  | 47  | 41  | 36  | 46  | 40  | 36  | 45  | 40  | 36  | 34  |  |  |   |
| 10  | 58  | 45  | 38  | 33  | 57  | 45  | 38  | 33  | 44  | 37  | 33  | 43  | 37  | 33  | 42  | 37  | 33  | 31  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   |
|-----|------|
| 0°  | 3875 |
| 5°  | 3900 |
| 10° | 3877 |
| 15° | 3753 |
| 20° | 3605 |
| 25° | 3425 |
| 30° | 3218 |
| 35° | 3002 |
| 40° | 2766 |
| 45° | 2499 |
| 50° | 2185 |
| 55° | 1836 |
| 60° | 1472 |
| 65° | 1179 |
| 70° | 1160 |
| 75° | 1093 |
| 80° | 1044 |
| 85° | 913  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle:  $45^\circ$

Luminance: 2499 cd/sqm

TEST NUMBER: P1504095

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-750LM)

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 36.6   | 4.9       |
| 10°-20°   | 101.3  | 13.5      |
| 20°-30°   | 141.7  | 18.8      |
| 30°-40°   | 152.5  | 20.3      |
| 40°-50°   | 135.1  | 18.0      |
| 50°-60°   | 94.2   | 12.5      |
| 60°-70°   | 51.7   | 6.9       |
| 70°-80°   | 29.8   | 4.0       |
| 80°-90°   | 8.9    | 1.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 279.6  | 37.2      |
| 0°-40°    | 432.1  | 57.5      |
| 0°-60°    | 661.3  | 88.0      |
| 0°-90°    | 751.8  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 751.8  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 385 |      |
| 5°  | 386 | 37   |
| 15° | 360 | 101  |
| 25° | 308 | 142  |
| 35° | 244 | 152  |
| 45° | 176 | 135  |
| 55° | 105 | 94   |
| 65° | 50  | 52   |
| 75° | 28  | 30   |
| 85° | 8   | 9    |
| 90° | 0   |      |

TEST NUMBER: P1504095

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-750LM)

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 384.8 |
| 2.5°  | 384.8 |
| 5°    | 385.9 |
| 7.5°  | 384.8 |
| 10°   | 379.2 |
| 12.5° | 371.3 |
| 15°   | 360.0 |
| 17.5° | 348.8 |
| 20°   | 336.4 |
| 22.5° | 322.9 |
| 25°   | 308.3 |
| 27.5° | 293.7 |
| 30°   | 276.8 |
| 32.5° | 261.0 |
| 35°   | 244.2 |
| 37.5° | 227.3 |
| 40°   | 210.4 |
| 42.5° | 193.5 |
| 45°   | 175.5 |
| 47.5° | 157.5 |
| 50°   | 139.5 |
| 52.5° | 122.6 |
| 55°   | 104.6 |
| 57.5° | 88.9  |
| 60°   | 73.1  |
| 62.5° | 59.6  |
| 65°   | 49.5  |
| 67.5° | 43.9  |
| 70°   | 39.4  |
| 72.5° | 33.8  |
| 75°   | 28.1  |
| 77.5° | 22.5  |
| 80°   | 18.0  |
| 82.5° | 12.4  |
| 85°   | 7.9   |
| 87.5° | 3.4   |
| 90°   | 0.0   |

(END OF REPORT)