

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504110

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-20)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, BRONZE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 576.4 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.22
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504110

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504110

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85		
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73		
3	92	82	75	69	90	81	74	68	78	72	67	75	70	66	73	68	65	62		
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48		
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	54	49	44	43		
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38		
8	64	51	43	37	62	50	42	37	49	42	37	47	41	36	46	41	36	34		
9	60	47	39	34	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	36	31	55	43	36	31	42	35	30	41	35	30	40	34	30	29		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2606
5°	2605
10°	2611
15°	2604
20°	2556
25°	2463
30°	2315
35°	2171
40°	2011
45°	1827
50°	1639
55°	1422
60°	1247
65°	1260
70°	1292
75°	1315
80°	1241
85°	1040

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1827 cd/sqm

TEST NUMBER: P1504110

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.6	4.3
10°-20°	70.3	12.2
20°-30°	101.6	17.6
30°-40°	110.1	19.1
40°-50°	98.9	17.2
50°-60°	73.1	12.7
60°-70°	52.1	9.0
70°-80°	34.8	6.0
80°-90°	10.9	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.5	34.1
0°-40°	306.6	53.2
0°-60°	478.6	83.0
0°-90°	576.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	259	
5°	258	25
15°	250	70
25°	222	102
35°	177	110
45°	128	99
55°	81	73
65°	53	52
75°	34	35
85°	9	11
90°	0	

TEST NUMBER: P1504110

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	258.8
2.5°	258.8
5°	257.7
7.5°	257.7
10°	255.4
12.5°	253.2
15°	249.8
17.5°	245.3
20°	238.5
22.5°	230.7
25°	221.7
27.5°	211.5
30°	199.1
32.5°	187.9
35°	176.6
37.5°	164.3
40°	153.0
42.5°	140.6
45°	128.3
47.5°	115.9
50°	104.6
52.5°	92.3
55°	81.0
57.5°	70.9
60°	61.9
62.5°	56.3
65°	52.9
67.5°	48.4
70°	43.9
72.5°	38.3
75°	33.8
77.5°	27.0
80°	21.4
82.5°	15.8
85°	9.0
87.5°	4.5
90°	0.0

(END OF REPORT)