

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503806

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 756.8 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503806

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503806

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	72	71		
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63		
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56		
6	78	66	59	53	76	65	58	53	64	57	52	62	56	52	61	56	52	50		
7	72	61	53	48	71	60	53	48	58	52	47	57	51	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41		
9	64	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	39	37		
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12091
5°	12081
10°	12055
15°	12007
20°	11814
25°	11704
30°	11423
35°	11071
40°	10261
45°	9093
50°	7522
55°	5559
60°	3410
65°	1043
70°	162
75°	214
80°	320
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9093 cd/sqm

TEST NUMBER: P1503806

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.1	4.9
10°-20°	105.9	14.0
20°-30°	158.1	20.9
30°-40°	182.4	24.1
40°-50°	159.2	21.0
50°-60°	92.9	12.3
60°-70°	19.1	2.5
70°-80°	1.9	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	301.0	39.8
0°-40°	483.4	63.9
0°-60°	735.5	97.2
0°-90°	756.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	756.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	392	
5°	390	37
15°	376	106
25°	344	158
35°	294	182
45°	208	159
55°	103	93
65°	14	19
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1503806

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	392.1
2.5°	392.1
5°	390.3
7.5°	388.6
10°	385.0
12.5°	381.4
15°	376.1
17.5°	368.9
20°	360.0
22.5°	352.9
25°	344.0
27.5°	333.3
30°	320.8
32.5°	310.1
35°	294.1
37.5°	274.5
40°	254.9
42.5°	231.7
45°	208.5
47.5°	181.8
50°	156.8
52.5°	130.1
55°	103.4
57.5°	78.4
60°	55.3
62.5°	32.1
65°	14.3
67.5°	3.6
70°	1.8
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)