

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503836

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 564.2 lumens
Efficiency: N/A
Efficacy: 49.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503836

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3000K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503836

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	102	98	107	103	100	96	99	96	93	95	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	54	48	72	61	53	48	59	52	47	58	52	47	56	51	46	45		
7	69	57	49	43	68	56	48	43	55	48	43	53	47	42	52	46	42	40		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33		
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8949
5°	8949
10°	8911
15°	8792
20°	8417
25°	7897
30°	7292
35°	6610
40°	5853
45°	5076
50°	4318
55°	3688
60°	3515
65°	3612
70°	3679
75°	3670
80°	3481
85°	3043

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5076 cd/sqm

TEST NUMBER: P1503836

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.5	4.9
10°-20°	77.1	13.7
20°-30°	106.5	18.9
30°-40°	109.4	19.4
40°-50°	90.0	16.0
50°-60°	62.9	11.2
60°-70°	48.8	8.7
70°-80°	32.3	5.7
80°-90°	9.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.0	37.4
0°-40°	320.5	56.8
0°-60°	473.4	83.9
0°-90°	564.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	290	
5°	289	27
15°	275	77
25°	232	106
35°	176	109
45°	116	90
55°	69	63
65°	50	49
75°	31	32
85°	9	10
90°	0	

TEST NUMBER: P1503836

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	290.2
2.5°	290.0
5°	289.1
7.5°	287.3
10°	284.6
12.5°	280.9
15°	275.4
17.5°	266.8
20°	256.5
22.5°	244.9
25°	232.1
27.5°	218.7
30°	204.8
32.5°	190.2
35°	175.6
37.5°	160.6
40°	145.4
42.5°	131.0
45°	116.4
47.5°	103.0
50°	90.0
52.5°	78.2
55°	68.6
57.5°	61.5
60°	57.0
62.5°	53.5
65°	49.5
67.5°	45.3
70°	40.8
72.5°	36.0
75°	30.8
77.5°	25.3
80°	19.6
82.5°	13.9
85°	8.6
87.5°	3.2
90°	0.0

(END OF REPORT)