

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504185

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-750LM)

Issue Date: 7/28/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1504185  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/28/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHITE-XX-OC (3500K-750LM)  
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR  
LIGHT LEVEL 1 - 750 NOMINAL LUMENS  
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 810.1 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.19  
Luminous Opening: Circular (Dia: 1.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1504185

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-750LM)

### Luminous Intensity Polar Plot





TEST NUMBER: P1504185

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-750LM)

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |
| 1   | 110 | 106 | 102 | 99  | 108 | 104 | 100 | 97  | 100 | 97  | 94  | 96  | 94  | 91  | 92  | 90  | 89  | 87  |  |  |
| 2   | 102 | 94  | 88  | 83  | 99  | 92  | 87  | 82  | 89  | 84  | 80  | 86  | 82  | 79  | 83  | 80  | 77  | 75  |  |  |
| 3   | 94  | 84  | 77  | 71  | 91  | 83  | 76  | 71  | 80  | 74  | 69  | 77  | 72  | 68  | 75  | 71  | 67  | 65  |  |  |
| 4   | 87  | 76  | 68  | 62  | 84  | 74  | 67  | 61  | 72  | 66  | 61  | 70  | 64  | 60  | 68  | 63  | 59  | 57  |  |  |
| 5   | 80  | 69  | 60  | 54  | 78  | 67  | 60  | 54  | 65  | 59  | 53  | 64  | 58  | 53  | 62  | 57  | 52  | 50  |  |  |
| 6   | 75  | 62  | 54  | 48  | 73  | 61  | 54  | 48  | 60  | 53  | 48  | 58  | 52  | 47  | 57  | 51  | 47  | 45  |  |  |
| 7   | 70  | 57  | 49  | 43  | 68  | 56  | 49  | 43  | 55  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 42  | 40  |  |  |
| 8   | 65  | 52  | 45  | 39  | 64  | 52  | 44  | 39  | 50  | 44  | 39  | 49  | 43  | 39  | 48  | 43  | 38  | 37  |  |  |
| 9   | 61  | 48  | 41  | 36  | 60  | 48  | 41  | 35  | 47  | 40  | 35  | 46  | 40  | 35  | 45  | 39  | 35  | 33  |  |  |
| 10  | 57  | 45  | 38  | 33  | 56  | 44  | 37  | 32  | 43  | 37  | 32  | 43  | 37  | 32  | 42  | 36  | 32  | 30  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   |
|-----|------|
| 0°  | 4090 |
| 5°  | 4106 |
| 10° | 4084 |
| 15° | 3964 |
| 20° | 3786 |
| 25° | 3625 |
| 30° | 3428 |
| 35° | 3195 |
| 40° | 2973 |
| 45° | 2691 |
| 50° | 2379 |
| 55° | 2015 |
| 60° | 1631 |
| 65° | 1368 |
| 70° | 1325 |
| 75° | 1268 |
| 80° | 1177 |
| 85° | 1040 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle:  $45^\circ$

Luminance: 2691 cd/sqm

TEST NUMBER: P1504185

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-750LM)

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 38.6   | 4.8       |
| 10°-20°   | 106.8  | 13.2      |
| 20°-30°   | 149.8  | 18.5      |
| 30°-40°   | 162.5  | 20.1      |
| 40°-50°   | 145.6  | 18.0      |
| 50°-60°   | 103.2  | 12.7      |
| 60°-70°   | 59.0   | 7.3       |
| 70°-80°   | 34.1   | 4.2       |
| 80°-90°   | 10.4   | 1.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 295.2  | 36.4      |
| 0°-40°    | 457.7  | 56.5      |
| 0°-60°    | 706.6  | 87.2      |
| 0°-90°    | 810.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 810.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 406 |      |
| 5°  | 406 | 39   |
| 15° | 380 | 107  |
| 25° | 326 | 150  |
| 35° | 260 | 163  |
| 45° | 189 | 146  |
| 55° | 115 | 103  |
| 65° | 57  | 59   |
| 75° | 33  | 34   |
| 85° | 9   | 10   |
| 90° | 0   |      |

TEST NUMBER: P1504185

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-750LM)

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 406.2 |
| 2.5°  | 406.2 |
| 5°    | 406.2 |
| 7.5°  | 405.0 |
| 10°   | 399.4 |
| 12.5° | 391.5 |
| 15°   | 380.3 |
| 17.5° | 367.9 |
| 20°   | 353.3 |
| 22.5° | 340.9 |
| 25°   | 326.3 |
| 27.5° | 310.5 |
| 30°   | 294.8 |
| 32.5° | 276.8 |
| 35°   | 259.9 |
| 37.5° | 243.0 |
| 40°   | 226.2 |
| 42.5° | 207.0 |
| 45°   | 189.0 |
| 47.5° | 171.0 |
| 50°   | 151.9 |
| 52.5° | 133.9 |
| 55°   | 114.8 |
| 57.5° | 97.9  |
| 60°   | 81.0  |
| 62.5° | 67.5  |
| 65°   | 57.4  |
| 67.5° | 50.6  |
| 70°   | 45.0  |
| 72.5° | 38.3  |
| 75°   | 32.6  |
| 77.5° | 25.9  |
| 80°   | 20.3  |
| 82.5° | 14.6  |
| 85°   | 9.0   |
| 87.5° | 4.5   |
| 90°   | 0.0   |

(END OF REPORT)