

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503913

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 666.6 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503913

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503913

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66			
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11055
5°	11010
10°	10925
15°	10567
20°	10051
25°	9486
30°	8852
35°	8169
40°	7411
45°	6589
50°	5666
55°	4726
60°	3811
65°	3407
70°	3219
75°	2943
80°	2681
85°	2441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6589 cd/sqm

TEST NUMBER: P1503913

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.8	5.1
10°-20°	92.8	13.9
20°-30°	128.1	19.2
30°-40°	135.4	20.3
40°-50°	116.3	17.5
50°-60°	79.1	11.9
60°-70°	46.7	7.0
70°-80°	26.6	4.0
80°-90°	7.7	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.7	38.2
0°-40°	390.1	58.5
0°-60°	585.6	87.9
0°-90°	666.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	358	
5°	356	34
15°	331	93
25°	279	128
35°	217	135
45°	151	116
55°	88	79
65°	47	47
75°	25	27
85°	7	8
90°	0	

TEST NUMBER: P1503913

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3000K-800LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	358.5
2.5°	357.1
5°	355.7
7.5°	354.4
10°	348.9
12.5°	340.6
15°	331.0
17.5°	318.7
20°	306.3
22.5°	292.6
25°	278.8
27.5°	265.1
30°	248.6
32.5°	233.5
35°	217.0
37.5°	200.5
40°	184.1
42.5°	167.6
45°	151.1
47.5°	134.6
50°	118.1
52.5°	103.0
55°	87.9
57.5°	74.2
60°	61.8
62.5°	52.2
65°	46.7
67.5°	41.2
70°	35.7
72.5°	30.2
75°	24.7
77.5°	20.6
80°	15.1
82.5°	11.0
85°	6.9
87.5°	2.7
90°	0.0

(END OF REPORT)