

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504186

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-22)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 969.2 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.19
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504186

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504186

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87		
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75		
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50		
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40		
8	65	52	45	39	64	52	44	39	50	44	39	49	43	39	48	43	38	37		
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33		
10	57	45	38	33	56	44	37	32	43	37	32	43	37	32	42	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4893
5°	4911
10°	4886
15°	4743
20°	4529
25°	4337
30°	4101
35°	3822
40°	3557
45°	3220
50°	2846
55°	2410
60°	1951
65°	1637
70°	1584
75°	1517
80°	1403
85°	1248

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3220 cd/sqm

TEST NUMBER: P1504186

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	4.8
10°-20°	127.7	13.2
20°-30°	179.3	18.5
30°-40°	194.4	20.1
40°-50°	174.2	18.0
50°-60°	123.5	12.7
60°-70°	70.6	7.3
70°-80°	40.8	4.2
80°-90°	12.5	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.2	36.4
0°-40°	547.6	56.5
0°-60°	845.3	87.2
0°-90°	969.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	486	
5°	486	46
15°	455	128
25°	390	179
35°	311	194
45°	226	174
55°	137	124
65°	69	71
75°	39	41
85°	11	12
90°	0	

TEST NUMBER: P1504186

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OC (3500K-900LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	485.9
2.5°	485.9
5°	485.9
7.5°	484.6
10°	477.9
12.5°	468.4
15°	455.0
17.5°	440.2
20°	422.7
22.5°	407.9
25°	390.4
27.5°	371.5
30°	352.7
32.5°	331.1
35°	310.9
37.5°	290.8
40°	270.6
42.5°	247.7
45°	226.1
47.5°	204.6
50°	181.7
52.5°	160.2
55°	137.3
57.5°	117.1
60°	96.9
62.5°	80.8
65°	68.7
67.5°	60.6
70°	53.8
72.5°	45.8
75°	39.0
77.5°	31.0
80°	24.2
82.5°	17.5
85°	10.8
87.5°	5.4
90°	0.0

(END OF REPORT)