

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503928

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHITE-XX-OT (3000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 535.9 lumens
Efficiency: N/A
Efficacy: 60.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503928

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503928

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85								
2	101	93	87	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73								
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63								
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55								
5	79	67	59	52	77	66	58	52	64	57	52	62	56	51	60	55	50	48								
6	73	61	53	46	72	60	52	46	58	51	46	57	50	46	55	49	45	43								
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39								
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35								
9	60	47	40	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32								
10	57	44	36	31	55	43	36	31	42	36	31	42	35	31	41	35	31	29								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7934
5°	7934
10°	7909
15°	7837
20°	7564
25°	7182
30°	6694
35°	6155
40°	5563
45°	4954
50°	4327
55°	3817
60°	3651
65°	3677
70°	3688
75°	3646
80°	3445
85°	2972

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4954 cd/sqm

TEST NUMBER: P1503928

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.3	4.5
10°-20°	68.8	12.8
20°-30°	96.8	18.1
30°-40°	102.0	19.0
40°-50°	87.7	16.4
50°-60°	64.8	12.1
60°-70°	49.7	9.3
70°-80°	32.1	6.0
80°-90°	9.6	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.0	35.4
0°-40°	292.0	54.5
0°-60°	444.5	82.9
0°-90°	535.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	535.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	257	
5°	256	24
15°	246	69
25°	211	97
35°	164	102
45°	114	88
55°	71	65
65°	50	50
75°	31	32
85°	8	10
90°	0	

TEST NUMBER: P1503928

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-800LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	257.3
2.5°	257.0
5°	256.3
7.5°	254.7
10°	252.6
12.5°	249.8
15°	245.5
17.5°	238.7
20°	230.5
22.5°	221.3
25°	211.1
27.5°	200.0
30°	188.0
32.5°	175.7
35°	163.5
37.5°	151.2
40°	138.2
42.5°	126.0
45°	113.6
47.5°	101.8
50°	90.2
52.5°	80.2
55°	71.0
57.5°	64.1
60°	59.2
62.5°	54.7
65°	50.4
67.5°	45.7
70°	40.9
72.5°	36.0
75°	30.6
77.5°	25.0
80°	19.4
82.5°	13.9
85°	8.4
87.5°	3.3
90°	0.0

(END OF REPORT)