

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504199

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-19)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1122.6 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.24
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504199

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504199

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62			
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54			
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47			
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34			
9	59	46	38	33	58	45	38	33	44	37	33	43	37	32	42	36	32	30			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4873
5°	4892
10°	4890
15°	4867
20°	4798
25°	4636
30°	4409
35°	4169
40°	3908
45°	3581
50°	3224
55°	2877
60°	2572
65°	2587
70°	2638
75°	2595
80°	2540
85°	2207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3581 cd/sqm

TEST NUMBER: P1504199

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.9	4.1
10°-20°	131.6	11.7
20°-30°	191.8	17.1
30°-40°	211.9	18.9
40°-50°	193.8	17.3
50°-60°	147.4	13.1
60°-70°	107.6	9.6
70°-80°	70.4	6.3
80°-90°	22.0	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.4	32.9
0°-40°	581.3	51.8
0°-60°	922.6	82.2
0°-90°	1122.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1122.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	484	
5°	484	46
15°	467	132
25°	417	192
35°	339	212
45°	252	194
55°	164	147
65°	109	108
75°	67	70
85°	19	22
90°	0	

TEST NUMBER: P1504199

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-1200LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	484.0
2.5°	484.0
5°	484.0
7.5°	480.2
10°	478.3
12.5°	474.5
15°	466.9
17.5°	459.3
20°	447.8
22.5°	434.5
25°	417.3
27.5°	400.2
30°	379.2
32.5°	360.2
35°	339.2
37.5°	318.2
40°	297.3
42.5°	274.4
45°	251.5
47.5°	228.7
50°	205.8
52.5°	184.8
55°	163.9
57.5°	144.8
60°	127.7
62.5°	118.2
65°	108.6
67.5°	99.1
70°	89.6
72.5°	78.1
75°	66.7
77.5°	55.3
80°	43.8
82.5°	32.4
85°	19.1
87.5°	7.6
90°	0.0

(END OF REPORT)