

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503962

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1145.1 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503962

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503962

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66		
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51		
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46		
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34		
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5901
5°	5941
10°	5905
15°	5717
20°	5490
25°	5217
30°	4902
35°	4571
40°	4213
45°	3808
50°	3329
55°	2798
60°	2243
65°	1796
70°	1766
75°	1665
80°	1589
85°	1386

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3808 cd/sqm

TEST NUMBER: P1503962

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.8	4.9
10°-20°	154.3	13.5
20°-30°	215.8	18.8
30°-40°	232.2	20.3
40°-50°	205.7	18.0
50°-60°	143.5	12.5
60°-70°	78.8	6.9
70°-80°	45.4	4.0
80°-90°	13.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.9	37.2
0°-40°	658.2	57.5
0°-60°	1007.4	88.0
0°-90°	1145.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1145.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	586	
5°	588	56
15°	548	154
25°	470	216
35°	372	232
45°	267	206
55°	159	143
65°	75	79
75°	43	45
85°	12	14
90°	0	

TEST NUMBER: P1503962

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-1200LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	586.1
2.5°	586.1
5°	587.8
7.5°	586.1
10°	577.5
12.5°	565.6
15°	548.4
17.5°	531.3
20°	512.4
22.5°	491.9
25°	469.6
27.5°	447.3
30°	421.6
32.5°	397.6
35°	371.9
37.5°	346.2
40°	320.5
42.5°	294.8
45°	267.4
47.5°	239.9
50°	212.5
52.5°	186.8
55°	159.4
57.5°	135.4
60°	111.4
62.5°	90.8
65°	75.4
67.5°	66.8
70°	60.0
72.5°	51.4
75°	42.8
77.5°	34.3
80°	27.4
82.5°	18.9
85°	12.0
87.5°	5.1
90°	0.0

(END OF REPORT)