

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503706

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, BRONZE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 390.3 lumens
Efficiency: N/A
Efficacy: 47.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503706

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503706

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	102	98	107	103	100	96	99	96	93	95	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	54	48	72	61	53	48	59	52	47	58	52	47	56	51	46	45		
7	69	57	49	43	68	56	48	43	55	48	43	53	47	42	52	46	42	40		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33		
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6189
5°	6191
10°	6165
15°	6082
20°	5821
25°	5461
30°	5045
35°	4570
40°	4050
45°	3511
50°	2989
55°	2554
60°	2436
65°	2503
70°	2542
75°	2538
80°	2415
85°	2087

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3511 cd/sqm

TEST NUMBER: P1503706

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.0	4.9
10°-20°	53.3	13.7
20°-30°	73.7	18.9
30°-40°	75.7	19.4
40°-50°	62.3	16.0
50°-60°	43.5	11.2
60°-70°	33.8	8.7
70°-80°	22.3	5.7
80°-90°	6.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	146.0	37.4
0°-40°	221.7	56.8
0°-60°	327.5	83.9
0°-90°	390.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	390.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	201	
5°	200	19
15°	190	53
25°	160	74
35°	121	76
45°	80	62
55°	48	44
65°	34	34
75°	21	22
85°	6	7
90°	0	

TEST NUMBER: P1503706

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-800LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	200.7
2.5°	200.6
5°	200.0
7.5°	198.8
10°	196.9
12.5°	194.3
15°	190.5
17.5°	184.6
20°	177.4
22.5°	169.4
25°	160.5
27.5°	151.3
30°	141.7
32.5°	131.6
35°	121.4
37.5°	111.1
40°	100.6
42.5°	90.6
45°	80.5
47.5°	71.3
50°	62.3
52.5°	54.1
55°	47.5
57.5°	42.5
60°	39.5
62.5°	37.0
65°	34.3
67.5°	31.3
70°	28.2
72.5°	24.9
75°	21.3
77.5°	17.5
80°	13.6
82.5°	9.6
85°	5.9
87.5°	2.2
90°	0.0

(END OF REPORT)