

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503721

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-ND (3500K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-ND (3500K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, BRASS REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 560.2 lumens
Efficiency: N/A
Efficacy: 68.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503721

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-ND (3500K-800LM)

Luminous Intensity Polar Plot



TEST NUMBER: P1503721

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-ND (3500K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20				
RC	80				70					50					30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90	
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79	
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70	
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61	
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55	
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49	
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	
8	67	55	47	42	66	54	47	42	53	46	42	52	46	42	51	45	41	40	
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	38	34	33	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8745
5°	8738
10°	8727
15°	8620
20°	8539
25°	8390
30°	8254
35°	7984
40°	7395
45°	6616
50°	5560
55°	4242
60°	2738
65°	1167
70°	559
75°	584
80°	444
85°	425

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6616 cd/sqm

TEST NUMBER: P1503721

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-ND (3500K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.8	4.8
10°-20°	76.2	13.6
20°-30°	113.8	20.3
30°-40°	131.6	23.5
40°-50°	116.2	20.7
50°-60°	70.7	12.6
60°-70°	18.9	3.4
70°-80°	4.7	0.8
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	216.9	38.7
0°-40°	348.4	62.2
0°-60°	535.3	95.5
0°-90°	560.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	560.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	284	
5°	282	27
15°	270	76
25°	247	114
35°	212	132
45°	152	116
55°	79	71
65°	16	19
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1503721

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-ND (3500K-800LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	283.6
2.5°	282.3
5°	282.3
7.5°	279.9
10°	278.7
12.5°	275.0
15°	270.0
17.5°	265.1
20°	260.2
22.5°	254.0
25°	246.6
27.5°	240.4
30°	231.8
32.5°	223.2
35°	212.1
37.5°	198.5
40°	183.7
42.5°	167.7
45°	151.7
47.5°	134.4
50°	115.9
52.5°	97.4
55°	78.9
57.5°	61.6
60°	44.4
62.5°	28.4
65°	16.0
67.5°	7.4
70°	6.2
72.5°	4.9
75°	4.9
77.5°	3.7
80°	2.5
82.5°	2.5
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)