

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503964

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 808.9 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503964

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-900LM)

Luminous Intensity Polar Plot



TEST NUMBER: P1503964

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66		
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	63	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51		
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46		
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34		
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4169
5°	4197
10°	4172
15°	4038
20°	3879
25°	3685
30°	3462
35°	3229
40°	2976
45°	2688
50°	2351
55°	1977
60°	1585
65°	1270
70°	1248
75°	1179
80°	1125
85°	982

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2688 cd/sqm

TEST NUMBER: P1503964

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	4.9
10°-20°	109.0	13.5
20°-30°	152.5	18.8
30°-40°	164.1	20.3
40°-50°	145.3	18.0
50°-60°	101.3	12.5
60°-70°	55.7	6.9
70°-80°	32.1	4.0
80°-90°	9.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.9	37.2
0°-40°	464.9	57.5
0°-60°	711.6	88.0
0°-90°	808.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	808.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	414	
5°	415	39
15°	387	109
25°	332	152
35°	263	164
45°	189	145
55°	113	101
65°	53	56
75°	30	32
85°	8	10
90°	0	

TEST NUMBER: P1503964

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-900LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	414.0
2.5°	414.0
5°	415.2
7.5°	414.0
10°	408.0
12.5°	399.5
15°	387.4
17.5°	375.3
20°	362.0
22.5°	347.4
25°	331.7
27.5°	316.0
30°	297.8
32.5°	280.9
35°	262.7
37.5°	244.5
40°	226.4
42.5°	208.2
45°	188.8
47.5°	169.5
50°	150.1
52.5°	132.0
55°	112.6
57.5°	95.6
60°	78.7
62.5°	64.2
65°	53.3
67.5°	47.2
70°	42.4
72.5°	36.3
75°	30.3
77.5°	24.2
80°	19.4
82.5°	13.3
85°	8.5
87.5°	3.6
90°	0.0

(END OF REPORT)