

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503766

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3500K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3500K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 691.6 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.3
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503766

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3500K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503766

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3500K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	83	77	72	81	75	70	78	73	69	76	71	68	66		
4	87	76	69	63	85	75	68	62	73	66	61	70	65	61	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	54	49	73	62	54	48	60	53	48	58	52	48	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	41		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9695
5°	9695
10°	9650
15°	9603
20°	9549
25°	9438
30°	9308
35°	9099
40°	8586
45°	7850
50°	6860
55°	5699
60°	4255
65°	2787
70°	2227
75°	2204
80°	2184
85°	1734

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7850 cd/sqm

TEST NUMBER: P1503766

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3500K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.7	4.3
10°-20°	84.9	12.3
20°-30°	127.7	18.5
30°-40°	150.2	21.7
40°-50°	138.1	20.0
50°-60°	94.5	13.7
60°-70°	41.0	5.9
70°-80°	19.5	2.8
80°-90°	6.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.4	35.0
0°-40°	392.5	56.8
0°-60°	625.1	90.4
0°-90°	691.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	691.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	314	
5°	313	30
15°	301	85
25°	277	128
35°	242	150
45°	180	138
55°	106	94
65°	38	41
75°	18	20
85°	5	6
90°	0	

TEST NUMBER: P1503766

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (3500K-800LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	314.4
2.5°	313.2
5°	313.2
7.5°	310.7
10°	308.2
12.5°	305.8
15°	300.8
17.5°	295.9
20°	291.0
22.5°	283.6
25°	277.4
27.5°	270.0
30°	261.4
32.5°	252.8
35°	241.7
37.5°	228.1
40°	213.3
42.5°	197.3
45°	180.0
47.5°	161.5
50°	143.0
52.5°	124.5
55°	106.0
57.5°	87.5
60°	69.0
62.5°	53.0
65°	38.2
67.5°	28.4
70°	24.7
72.5°	21.0
75°	18.5
77.5°	16.0
80°	12.3
82.5°	8.6
85°	4.9
87.5°	2.5
90°	0.0

(END OF REPORT)