

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504067

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-19)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1009.5 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.24
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504067

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504067

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72			
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62			
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54			
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47			
6	72	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34			
9	59	46	38	33	58	45	38	33	44	37	33	43	37	32	42	36	32	30			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4383
5°	4400
10°	4399
15°	4377
20°	4315
25°	4170
30°	3965
35°	3750
40°	3515
45°	3221
50°	2900
55°	2588
60°	2312
65°	2328
70°	2370
75°	2334
80°	2285
85°	1976

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3221 cd/sqm

TEST NUMBER: P1504067

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.3	4.1
10°-20°	118.4	11.7
20°-30°	172.5	17.1
30°-40°	190.6	18.9
40°-50°	174.3	17.3
50°-60°	132.6	13.1
60°-70°	96.7	9.6
70°-80°	63.3	6.3
80°-90°	19.8	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.2	32.9
0°-40°	522.8	51.8
0°-60°	829.7	82.2
0°-90°	1009.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	435	
5°	435	41
15°	420	118
25°	375	172
35°	305	191
45°	226	174
55°	147	133
65°	98	97
75°	60	63
85°	17	20
90°	0	

TEST NUMBER: P1504067

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1200LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	435.3
2.5°	435.3
5°	435.3
7.5°	431.9
10°	430.2
12.5°	426.7
15°	419.9
17.5°	413.0
20°	402.7
22.5°	390.7
25°	375.3
27.5°	359.9
30°	341.0
32.5°	323.9
35°	305.1
37.5°	286.2
40°	267.4
42.5°	246.8
45°	226.2
47.5°	205.7
50°	185.1
52.5°	166.2
55°	147.4
57.5°	130.2
60°	114.8
62.5°	106.3
65°	97.7
67.5°	89.1
70°	80.5
72.5°	70.3
75°	60.0
77.5°	49.7
80°	39.4
82.5°	29.1
85°	17.1
87.5°	6.9
90°	0.0

(END OF REPORT)