

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504084

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (4000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504084
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-17)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (4000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 909.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504084

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (4000K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504084

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (4000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89						
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	79	78						
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68						
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59						
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52						
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46						
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41						
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37						
9	61	48	41	35	60	48	40	35	47	40	35	46	39	35	45	39	35	33						
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4081
5°	4083
10°	4074
15°	4055
20°	4024
25°	3991
30°	3924
35°	3882
40°	3830
45°	3725
50°	3376
55°	2832
60°	2102
65°	1196
70°	238
75°	54
80°	81
85°	162

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3725 cd/sqm

TEST NUMBER: P1504084

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (4000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.4	4.2
10°-20°	109.7	12.1
20°-30°	165.4	18.2
30°-40°	197.6	21.7
40°-50°	199.4	21.9
50°-60°	143.4	15.8
60°-70°	51.4	5.7
70°-80°	2.7	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	313.5	34.5
0°-40°	511.1	56.2
0°-60°	854.0	93.9
0°-90°	909.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	909.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	405	
5°	404	38
15°	389	110
25°	359	165
35°	316	198
45°	262	199
55°	161	143
65°	50	51
75°	1	3
85°	1	1
90°	0	

TEST NUMBER: P1504084

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (4000K-900LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	405.3
2.5°	404.0
5°	404.0
7.5°	401.2
10°	398.5
12.5°	394.5
15°	389.0
17.5°	382.3
20°	375.5
22.5°	368.7
25°	359.2
27.5°	349.7
30°	337.5
32.5°	326.7
35°	315.8
37.5°	305.0
40°	291.4
42.5°	279.2
45°	261.6
47.5°	239.9
50°	215.5
52.5°	189.8
55°	161.3
57.5°	132.8
60°	104.4
62.5°	77.3
65°	50.2
67.5°	25.8
70°	8.1
72.5°	2.7
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)