

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504098

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504098
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 757.1 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504098

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504098

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46			
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34			
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3902
5°	3928
10°	3904
15°	3780
20°	3630
25°	3450
30°	3240
35°	3023
40°	2785
45°	2518
50°	2201
55°	1850
60°	1482
65°	1189
70°	1169
75°	1101
80°	1050
85°	913

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2518 cd/sqm

TEST NUMBER: P1504098

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	4.9
10°-20°	102.0	13.5
20°-30°	142.7	18.8
30°-40°	153.6	20.3
40°-50°	136.0	18.0
50°-60°	94.8	12.5
60°-70°	52.1	6.9
70°-80°	30.0	4.0
80°-90°	8.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.6	37.2
0°-40°	435.1	57.5
0°-60°	666.0	88.0
0°-90°	757.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	757.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	388	
5°	389	37
15°	363	102
25°	310	143
35°	246	154
45°	177	136
55°	105	95
65°	50	52
75°	28	30
85°	8	9
90°	0	

TEST NUMBER: P1504098

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	387.5
2.5°	387.5
5°	388.6
7.5°	387.5
10°	381.8
12.5°	373.9
15°	362.6
17.5°	351.3
20°	338.8
22.5°	325.2
25°	310.5
27.5°	295.7
30°	278.7
32.5°	262.9
35°	245.9
37.5°	228.9
40°	211.9
42.5°	194.9
45°	176.8
47.5°	158.6
50°	140.5
52.5°	123.5
55°	105.4
57.5°	89.5
60°	73.6
62.5°	60.1
65°	49.9
67.5°	44.2
70°	39.7
72.5°	34.0
75°	28.3
77.5°	22.7
80°	18.1
82.5°	12.5
85°	7.9
87.5°	3.4
90°	0.0

(END OF REPORT)