

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503826

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-14)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 592.2 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503826

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503826

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10077
5°	10076
10°	10020
15°	9647
20°	9155
25°	8656
30°	8033
35°	7363
40°	6662
45°	5844
50°	4922
55°	3968
60°	3121
65°	2795
70°	2714
75°	2609
80°	2433
85°	1946

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5844 cd/sqm

TEST NUMBER: P1503826

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.0	5.2
10°-20°	84.8	14.3
20°-30°	116.6	19.7
30°-40°	122.1	20.6
40°-50°	102.9	17.4
50°-60°	67.0	11.3
60°-70°	38.4	6.5
70°-80°	22.7	3.8
80°-90°	6.7	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.4	39.2
0°-40°	354.5	59.9
0°-60°	524.4	88.5
0°-90°	592.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	592.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	327	
5°	326	31
15°	302	85
25°	254	117
35°	196	122
45°	134	103
55°	74	67
65°	38	38
75°	22	23
85°	6	7
90°	0	

TEST NUMBER: P1503826

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (3500K-800LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	326.8
2.5°	326.8
5°	325.5
7.5°	325.5
10°	320.0
12.5°	311.8
15°	302.2
17.5°	291.3
20°	279.0
22.5°	266.7
25°	254.4
27.5°	240.7
30°	225.6
32.5°	210.6
35°	195.6
37.5°	180.5
40°	165.5
42.5°	149.1
45°	134.0
47.5°	117.6
50°	102.6
52.5°	88.9
55°	73.8
57.5°	61.5
60°	50.6
62.5°	42.4
65°	38.3
67.5°	34.2
70°	30.1
72.5°	26.0
75°	21.9
77.5°	16.4
80°	13.7
82.5°	9.6
85°	5.5
87.5°	2.7
90°	0.0

(END OF REPORT)