

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503839

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 561.7 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503839

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503839

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	102	98	107	103	100	96	99	96	93	95	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	54	48	72	61	53	48	59	52	47	58	52	47	56	51	46	45		
7	69	57	49	43	68	56	48	43	55	48	43	53	47	42	52	46	42	40		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33		
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8909
5°	8909
10°	8874
15°	8754
20°	8378
25°	7860
30°	7260
35°	6580
40°	5829
45°	5054
50°	4298
55°	3672
60°	3503
65°	3597
70°	3660
75°	3658
80°	3463
85°	3007

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5054 cd/sqm

TEST NUMBER: P1503839

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.3	4.9
10°-20°	76.8	13.7
20°-30°	106.0	18.9
30°-40°	109.0	19.4
40°-50°	89.7	16.0
50°-60°	62.7	11.2
60°-70°	48.6	8.7
70°-80°	32.1	5.7
80°-90°	9.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.1	37.4
0°-40°	319.0	56.8
0°-60°	471.4	83.9
0°-90°	561.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	561.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	289	
5°	288	27
15°	274	77
25°	231	106
35°	175	109
45°	116	90
55°	68	63
65°	49	49
75°	31	32
85°	8	10
90°	0	

TEST NUMBER: P1503839

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OT (3500K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	288.9
2.5°	288.7
5°	287.8
7.5°	286.0
10°	283.4
12.5°	279.7
15°	274.2
17.5°	265.6
20°	255.3
22.5°	243.8
25°	231.0
27.5°	217.7
30°	203.9
32.5°	189.3
35°	174.8
37.5°	159.9
40°	144.8
42.5°	130.4
45°	115.9
47.5°	102.6
50°	89.6
52.5°	77.9
55°	68.3
57.5°	61.2
60°	56.8
62.5°	53.2
65°	49.3
67.5°	45.1
70°	40.6
72.5°	35.8
75°	30.7
77.5°	25.2
80°	19.5
82.5°	13.8
85°	8.5
87.5°	3.2
90°	0.0

(END OF REPORT)