

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503885

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3500K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3500K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, BRASS REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 356.7 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503885

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3500K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503885

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3500K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44		
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40		
8	65	52	44	39	63	51	44	39	50	43	38	49	43	38	48	42	38	36		
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5600
5°	5603
10°	5577
15°	5507
20°	5280
25°	4961
30°	4579
35°	4163
40°	3711
45°	3223
50°	2754
55°	2366
60°	2257
65°	2313
70°	2344
75°	2323
80°	2202
85°	1875

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3223 cd/sqm

TEST NUMBER: P1503885

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3500K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.2	4.8
10°-20°	48.3	13.5
20°-30°	66.9	18.7
30°-40°	69.0	19.3
40°-50°	57.2	16.0
50°-60°	40.4	11.3
60°-70°	31.3	8.8
70°-80°	20.5	5.7
80°-90°	6.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	132.4	37.1
0°-40°	201.3	56.4
0°-60°	298.9	83.8
0°-90°	356.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	356.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	182	
5°	181	17
15°	172	48
25°	146	67
35°	111	69
45°	74	57
55°	44	40
65°	32	31
75°	20	20
85°	5	6
90°	0	

TEST NUMBER: P1503885

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OT (3500K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	181.6
2.5°	181.5
5°	181.0
7.5°	179.8
10°	178.1
12.5°	175.8
15°	172.5
17.5°	167.2
20°	160.9
22.5°	153.6
25°	145.8
27.5°	137.6
30°	128.6
32.5°	119.7
35°	110.6
37.5°	101.4
40°	92.2
42.5°	83.1
45°	73.9
47.5°	65.5
50°	57.4
52.5°	50.3
55°	44.0
57.5°	39.5
60°	36.6
62.5°	34.2
65°	31.7
67.5°	29.0
70°	26.0
72.5°	22.9
75°	19.5
77.5°	16.1
80°	12.4
82.5°	8.8
85°	5.3
87.5°	2.0
90°	0.0

(END OF REPORT)