

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504173

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (4000K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-16)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (4000K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 911.9 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.38
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504173

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (4000K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504173

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (4000K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	94	88	83	99	93	87	82	89	84	80	86	82	79	83	80	77	75		
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	61	55	51	49		
6	73	61	52	46	72	60	52	46	58	51	46	57	50	45	55	49	45	43		
7	68	55	47	41	66	55	47	41	53	46	41	52	45	40	50	45	40	38		
8	63	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34		
9	59	46	39	33	58	46	38	33	45	38	33	44	37	33	43	37	33	31		
10	56	43	35	30	54	42	35	30	41	35	30	40	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3765
5°	3756
10°	3753
15°	3744
20°	3728
25°	3714
30°	3675
35°	3649
40°	3634
45°	3550
50°	3302
55°	2904
60°	2328
65°	1646
70°	901
75°	751
80°	789
85°	786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3550 cd/sqm

TEST NUMBER: P1504173

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (4000K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.3	3.9
10°-20°	101.4	11.1
20°-30°	153.8	16.9
30°-40°	185.9	20.4
40°-50°	190.8	20.9
50°-60°	146.8	16.1
60°-70°	69.3	7.6
70°-80°	21.4	2.3
80°-90°	7.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.5	31.9
0°-40°	476.4	52.2
0°-60°	814.1	89.3
0°-90°	911.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	911.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	374	
5°	372	35
15°	359	101
25°	334	154
35°	297	186
45°	249	191
55°	165	147
65°	69	69
75°	19	21
85°	7	7
90°	0	

TEST NUMBER: P1504173

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-WHTE-XX-ND (4000K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	373.9
2.5°	372.8
5°	371.6
7.5°	369.4
10°	367.1
12.5°	363.7
15°	359.2
17.5°	354.6
20°	347.9
22.5°	341.1
25°	334.3
27.5°	325.2
30°	316.1
32.5°	307.1
35°	296.9
37.5°	286.7
40°	276.5
42.5°	265.1
45°	249.3
47.5°	231.1
50°	210.8
52.5°	189.2
55°	165.4
57.5°	140.5
60°	115.6
62.5°	91.8
65°	69.1
67.5°	47.6
70°	30.6
72.5°	22.7
75°	19.3
77.5°	17.0
80°	13.6
82.5°	10.2
85°	6.8
87.5°	2.3
90°	0.0

(END OF REPORT)