

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503951

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (5000K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-17)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (5000K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 694.4 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503951

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (5000K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503951

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (5000K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78		
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68		
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59		
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52		
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46		
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37		
9	61	48	41	35	60	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3117
5°	3119
10°	3113
15°	3098
20°	3074
25°	3049
30°	2999
35°	2966
40°	2926
45°	2847
50°	2580
55°	2163
60°	1605
65°	913
70°	183
75°	39
80°	58
85°	116

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2847 cd/sqm

TEST NUMBER: P1503951

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (5000K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.3	4.2
10°-20°	83.8	12.1
20°-30°	126.4	18.2
30°-40°	151.0	21.7
40°-50°	152.4	21.9
50°-60°	109.6	15.8
60°-70°	39.2	5.6
70°-80°	2.0	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.5	34.5
0°-40°	390.5	56.2
0°-60°	652.5	94.0
0°-90°	694.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	694.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	310	
5°	309	29
15°	297	84
25°	274	126
35°	241	151
45°	200	152
55°	123	110
65°	38	39
75°	1	2
85°	1	1
90°	0	

TEST NUMBER: P1503951

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (5000K-750LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	309.6
2.5°	308.6
5°	308.6
7.5°	306.5
10°	304.5
12.5°	301.4
15°	297.2
17.5°	292.0
20°	286.9
22.5°	281.7
25°	274.4
27.5°	267.2
30°	257.9
32.5°	249.6
35°	241.3
37.5°	233.0
40°	222.6
42.5°	213.3
45°	199.9
47.5°	183.3
50°	164.7
52.5°	145.0
55°	123.2
57.5°	101.5
60°	79.7
62.5°	59.0
65°	38.3
67.5°	19.7
70°	6.2
72.5°	2.1
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)