

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503693

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-14)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 424.8 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503693

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503693

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76		
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59		
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7228
5°	7228
10°	7186
15°	6921
20°	6566
25°	6209
30°	5765
35°	5281
40°	4778
45°	4191
50°	3531
55°	2849
60°	2239
65°	2007
70°	1947
75°	1871
80°	1740
85°	1380

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4191 cd/sqm

TEST NUMBER: P1503693

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.2	5.2
10°-20°	60.8	14.3
20°-30°	83.7	19.7
30°-40°	87.6	20.6
40°-50°	73.8	17.4
50°-60°	48.1	11.3
60°-70°	27.5	6.5
70°-80°	16.3	3.8
80°-90°	4.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	166.7	39.2
0°-40°	254.3	59.9
0°-60°	376.2	88.5
0°-90°	424.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	424.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	234	
5°	234	22
15°	217	61
25°	182	84
35°	140	88
45°	96	74
55°	53	48
65°	28	28
75°	16	16
85°	4	5
90°	0	

TEST NUMBER: P1503693

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (4000K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	234.4
2.5°	234.4
5°	233.5
7.5°	233.5
10°	229.5
12.5°	223.7
15°	216.8
17.5°	208.9
20°	200.1
22.5°	191.3
25°	182.5
27.5°	172.6
30°	161.9
32.5°	151.1
35°	140.3
37.5°	129.5
40°	118.7
42.5°	106.9
45°	96.1
47.5°	84.4
50°	73.6
52.5°	63.8
55°	53.0
57.5°	44.1
60°	36.3
62.5°	30.4
65°	27.5
67.5°	24.5
70°	21.6
72.5°	18.6
75°	15.7
77.5°	11.8
80°	9.8
82.5°	6.9
85°	3.9
87.5°	2.0
90°	0.0

(END OF REPORT)