

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503965

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-1200LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-23)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-1200LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1200 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1172.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.18
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503965

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-1200LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503965

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-1200LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	73	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46			
7	70	58	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34			
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6040
5°	6081
10°	6044
15°	5851
20°	5619
25°	5339
30°	5017
35°	4678
40°	4311
45°	3896
50°	3407
55°	2863
60°	2296
65°	1839
70°	1808
75°	1704
80°	1629
85°	1421

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3896 cd/sqm

TEST NUMBER: P1503965

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-1200LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	4.9
10°-20°	157.9	13.5
20°-30°	220.9	18.8
30°-40°	237.7	20.3
40°-50°	210.6	18.0
50°-60°	146.8	12.5
60°-70°	80.6	6.9
70°-80°	46.5	4.0
80°-90°	13.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.9	37.2
0°-40°	673.6	57.5
0°-60°	1031.0	88.0
0°-90°	1172.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1172.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	600	
5°	602	57
15°	561	158
25°	481	221
35°	381	238
45°	274	211
55°	163	147
65°	77	81
75°	44	46
85°	12	14
90°	0	

TEST NUMBER: P1503965

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-1200LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	599.9
2.5°	599.9
5°	601.6
7.5°	599.9
10°	591.1
12.5°	578.8
15°	561.3
17.5°	543.7
20°	524.4
22.5°	503.4
25°	480.6
27.5°	457.8
30°	431.5
32.5°	406.9
35°	380.6
37.5°	354.3
40°	328.0
42.5°	301.7
45°	273.6
47.5°	245.6
50°	217.5
52.5°	191.2
55°	163.1
57.5°	138.6
60°	114.0
62.5°	93.0
65°	77.2
67.5°	68.4
70°	61.4
72.5°	52.6
75°	43.8
77.5°	35.1
80°	28.1
82.5°	19.3
85°	12.3
87.5°	5.3
90°	0.0

(END OF REPORT)