

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503797

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 630.3 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503797

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503797

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85								
2	101	93	87	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73								
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63								
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55								
5	79	67	59	52	77	66	58	52	64	57	52	62	56	51	60	55	50	48								
6	73	61	53	46	72	60	52	46	58	51	46	57	50	46	55	49	45	43								
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39								
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35								
9	60	47	40	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32								
10	57	44	36	31	55	43	36	31	42	36	31	42	35	31	41	35	31	29								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9331
5°	9333
10°	9303
15°	9216
20°	8896
25°	8448
30°	7876
35°	7239
40°	6541
45°	5826
50°	5090
55°	4489
60°	4292
65°	4327
70°	4337
75°	4289
80°	4049
85°	3503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5826 cd/sqm

TEST NUMBER: P1503797

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.6	4.5
10°-20°	80.9	12.8
20°-30°	113.9	18.1
30°-40°	120.0	19.0
40°-50°	103.1	16.4
50°-60°	76.2	12.1
60°-70°	58.5	9.3
70°-80°	37.8	6.0
80°-90°	11.3	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.4	35.4
0°-40°	343.5	54.5
0°-60°	522.8	82.9
0°-90°	630.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	630.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	303	
5°	302	29
15°	289	81
25°	248	114
35°	192	120
45°	134	103
55°	84	76
65°	59	58
75°	36	38
85°	10	11
90°	0	

TEST NUMBER: P1503797

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (4000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	302.6
2.5°	302.3
5°	301.5
7.5°	299.5
10°	297.1
12.5°	293.9
15°	288.7
17.5°	280.8
20°	271.1
22.5°	260.3
25°	248.3
27.5°	235.2
30°	221.2
32.5°	206.6
35°	192.3
37.5°	177.9
40°	162.5
42.5°	148.2
45°	133.6
47.5°	119.7
50°	106.1
52.5°	94.4
55°	83.5
57.5°	75.4
60°	69.6
62.5°	64.3
65°	59.3
67.5°	53.8
70°	48.1
72.5°	42.3
75°	36.0
77.5°	29.4
80°	22.8
82.5°	16.3
85°	9.9
87.5°	3.9
90°	0.0

(END OF REPORT)