

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503828

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-14)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 466.6 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503828

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503828

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7940
5°	7937
10°	7894
15°	7601
20°	7213
25°	6818
30°	6331
35°	5801
40°	5249
45°	4605
50°	3876
55°	3129
60°	2461
65°	2204
70°	2137
75°	2049
80°	1918
85°	1521

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4605 cd/sqm

TEST NUMBER: P1503828

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.4	5.2
10°-20°	66.8	14.3
20°-30°	91.9	19.7
30°-40°	96.2	20.6
40°-50°	81.0	17.4
50°-60°	52.8	11.3
60°-70°	30.3	6.5
70°-80°	17.9	3.8
80°-90°	5.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.1	39.2
0°-40°	279.3	59.9
0°-60°	413.1	88.5
0°-90°	466.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	466.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	258	
5°	256	24
15°	238	67
25°	200	92
35°	154	96
45°	106	81
55°	58	53
65°	30	30
75°	17	18
85°	4	5
90°	0	

TEST NUMBER: P1503828

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (4000K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	257.5
2.5°	257.5
5°	256.4
7.5°	256.4
10°	252.1
12.5°	245.6
15°	238.1
17.5°	229.5
20°	219.8
22.5°	210.1
25°	200.4
27.5°	189.6
30°	177.8
32.5°	165.9
35°	154.1
37.5°	142.2
40°	130.4
42.5°	117.4
45°	105.6
47.5°	92.7
50°	80.8
52.5°	70.0
55°	58.2
57.5°	48.5
60°	39.9
62.5°	33.4
65°	30.2
67.5°	26.9
70°	23.7
72.5°	20.5
75°	17.2
77.5°	12.9
80°	10.8
82.5°	7.5
85°	4.3
87.5°	2.2
90°	0.0

(END OF REPORT)