

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1504087

Luminaire Tested: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (5000K-900LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1504087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-17)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (5000K-900LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR
LIGHT LEVEL 2 - 900 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 921.7 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1504087

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (5000K-900LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1504087

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (5000K-900LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	79	78			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68			
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59			
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52			
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46			
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			
9	61	48	41	35	60	48	40	35	47	40	35	46	39	35	45	39	35	33			
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4138
5°	4140
10°	4132
15°	4112
20°	4079
25°	4046
30°	3980
35°	3937
40°	3884
45°	3778
50°	3423
55°	2872
60°	2131
65°	1213
70°	241
75°	54
80°	81
85°	162

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3778 cd/sqm

TEST NUMBER: P1504087

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (5000K-900LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.9	4.2
10°-20°	111.2	12.1
20°-30°	167.8	18.2
30°-40°	200.4	21.7
40°-50°	202.2	21.9
50°-60°	145.5	15.8
60°-70°	52.0	5.6
70°-80°	2.7	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	317.9	34.5
0°-40°	518.3	56.2
0°-60°	866.0	94.0
0°-90°	921.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	921.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	411	
5°	410	39
15°	394	111
25°	364	168
35°	320	200
45°	265	202
55°	164	145
65°	51	52
75°	1	3
85°	1	1
90°	0	

TEST NUMBER: P1504087

CATALOG NUMBER: PRLX-SM6-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (5000K-900LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	411.0
2.5°	409.6
5°	409.6
7.5°	406.9
10°	404.1
12.5°	400.0
15°	394.5
17.5°	387.6
20°	380.7
22.5°	373.9
25°	364.2
27.5°	354.6
30°	342.3
32.5°	331.3
35°	320.3
37.5°	309.3
40°	295.5
42.5°	283.2
45°	265.3
47.5°	243.3
50°	218.5
52.5°	192.4
55°	163.6
57.5°	134.7
60°	105.8
62.5°	78.3
65°	50.9
67.5°	26.1
70°	8.2
72.5°	2.7
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)