

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503918

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (4000K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (4000K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 522.9 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503918

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (4000K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503918

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (4000K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66			
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8671
5°	8636
10°	8570
15°	8291
20°	7886
25°	7441
30°	6943
35°	6407
40°	5813
45°	5168
50°	4447
55°	3710
60°	2991
65°	2671
70°	2524
75°	2311
80°	2113
85°	1911

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5168 cd/sqm

TEST NUMBER: P1503918

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (4000K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	5.1
10°-20°	72.8	13.9
20°-30°	100.5	19.2
30°-40°	106.2	20.3
40°-50°	91.2	17.4
50°-60°	62.1	11.9
60°-70°	36.6	7.0
70°-80°	20.9	4.0
80°-90°	6.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	199.8	38.2
0°-40°	306.0	58.5
0°-60°	459.4	87.8
0°-90°	522.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	522.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	281	
5°	279	27
15°	260	73
25°	219	101
35°	170	106
45°	118	91
55°	69	62
65°	37	37
75°	19	21
85°	5	6
90°	0	

TEST NUMBER: P1503918

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (4000K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	281.2
2.5°	280.1
5°	279.0
7.5°	278.0
10°	273.7
12.5°	267.2
15°	259.7
17.5°	250.0
20°	240.3
22.5°	229.5
25°	218.7
27.5°	207.9
30°	195.0
32.5°	183.2
35°	170.2
37.5°	157.3
40°	144.4
42.5°	131.4
45°	118.5
47.5°	105.6
50°	92.7
52.5°	80.8
55°	69.0
57.5°	58.2
60°	48.5
62.5°	40.9
65°	36.6
67.5°	32.3
70°	28.0
72.5°	23.7
75°	19.4
77.5°	16.2
80°	11.9
82.5°	8.6
85°	5.4
87.5°	2.2
90°	0.0

(END OF REPORT)