

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503696

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-14)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 437.2 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503696

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503696

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76					76			
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67					67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59					59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7441
5°	7438
10°	7396
15°	7122
20°	6757
25°	6390
30°	5932
35°	5436
40°	4919
45°	4313
50°	3632
55°	2930
60°	2307
65°	2065
70°	2002
75°	1930
80°	1794
85°	1415

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4313 cd/sqm

TEST NUMBER: P1503696

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.9	5.2
10°-20°	62.6	14.3
20°-30°	86.1	19.7
30°-40°	90.2	20.6
40°-50°	75.9	17.4
50°-60°	49.5	11.3
60°-70°	28.3	6.5
70°-80°	16.8	3.8
80°-90°	4.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.6	39.2
0°-40°	261.7	59.9
0°-60°	387.1	88.5
0°-90°	437.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	437.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	241	
5°	240	23
15°	223	63
25°	188	86
35°	144	90
45°	99	76
55°	54	49
65°	28	28
75°	16	17
85°	4	5
90°	0	

TEST NUMBER: P1503696

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OC (5000K-650LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	241.3
2.5°	241.3
5°	240.3
7.5°	240.3
10°	236.2
12.5°	230.2
15°	223.1
17.5°	215.0
20°	205.9
22.5°	196.9
25°	187.8
27.5°	177.7
30°	166.6
32.5°	155.5
35°	144.4
37.5°	133.3
40°	122.2
42.5°	110.0
45°	98.9
47.5°	86.8
50°	75.7
52.5°	65.6
55°	54.5
57.5°	45.4
60°	37.4
62.5°	31.3
65°	28.3
67.5°	25.2
70°	22.2
72.5°	19.2
75°	16.2
77.5°	12.1
80°	10.1
82.5°	7.1
85°	4.0
87.5°	2.0
90°	0.0

(END OF REPORT)